

10 x 10mm, 300µm Pitch, 10.1° Divergence, Cyl. Microlens Array



Stock **#86-841** **1 In Stock**

⊖ 1 ⊕ £665⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£665.00 each
Qty 11-25	£585.00 each
Qty 26-49	£558.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Array **Type:**

Physical & Mechanical Properties

10.0 x 10.0 ±0.05 **Dimensions (mm):**

0.380 **Radius R (mm):**

1.20 ±0.05	Thickness (mm):
Optical Properties	
0.80	Effective Focal Length EFL (mm):
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
Uncoated	Coating:
200 - 2200	Wavelength Range (nm):
±10.1	Divergence Angle (°):
300.00 ±0.25	Pitch (µm):
Single-Sided	Array Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.

;