

## 12 x 12mm, 500µm Pitch, 2.3° Divergence, Cyl. Microlens Array



Stock #23-871 **2 In Stock**

£510.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	£510.00 each
Qty 11-25	£459.00 each
Qty 26-49	£437.00 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Type:  
Lens Array

### Physical & Mechanical Properties

Dimensions (mm):  
12.0 x 12.0 ±0.10

Radius R (mm):  
5.500

2.00 ±0.1      **Thickness (mm):**

## Optical Properties

12.20 @ 1064nm      **Effective Focal Length EFL (mm):**

[Fused Silica](#) (Corning 7980)      **Substrate:**

Uncoated      **Coating:**

200 - 2200      **Wavelength Range (nm):**

2.3 (Full Width)      **Divergence Angle (°):**

500      **Pitch (µm):**

Single-Sided      **Array Type:**

## Regulatory Compliance

[Compliant](#)      **RoHS 2015:**

[View](#)      **Certificate of Conformance:**

[Compliant](#)      **Reach 250:**

## Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.