

[See all 17 Products in Family](#)

TECHSPEC®

1000 - 1060nm, 50.8mm Dia., Ultrafast Mirror



Stock #14-847

CONTACT US

-

1

+

£464^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	£464.00 each
Qty 10+	£408.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Laser Mirror	Type:
Yb:doped Lasers 1st Harmonic	Typical Applications:
Physical & Mechanical Properties	
80	Clear Aperture (%):

Commercial Polish	Back Surface:
50.80 +0.00/-0.10	Diameter (mm):
9.52 ±0.10	Thickness (mm):
<10	Parallelism (arcsec):
Optical Properties	
10-5	Surface Quality:
R _s >99.95% @ 1000 - 1060nm R _p >99.9% @ 1000 - 1060nm	Coating Specification:
0 ±20fs ² @ 1000 - 1060nm (s-pol & p-pol)	GDD Specification:
1000 - 1060	Wavelength Range (nm):
λ/8	Surface Flatness (P-V):
Dielectric	Coating Type:
Ultrafast (1000-1060nm)	Coating:
1030	Design Wavelength DWL (nm):
45	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate: □
0.45 J/cm ² @ 1030nm, 207fs, 1 pulse 0.35 J/cm ² @ 1030nm, 207fs, 1,000 pulses	Damage Threshold, By Design: □

Regulatory Compliance	
View	Certificate of Conformance:


Product Details

- Designed with High Reflectivity for Ultrafast Beam Steering
- Ion-Beam Sputtered Coating for Low Scatter and Absorption
- GDD as Low as 0±20fs² at Design Wavelength Range

TECHSPEC® High Performance Low GDD Ultrafast Mirrors are designed to have high reflectivity at 0° or 45° angles of incidence, making them ideal for ultrafast laser beam steering applications. These mirrors have a dispersion compensating coating obtained through a precision ion beam sputtering (IBS) process, providing lower scatter and absorption than traditional dielectric laser mirrors. TECHSPEC High Performance Low GDD Ultrafast Mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. Typical applications include use in the transport of femtosecond laser pulses.

Note: Please [contact us](#) if your application requires a TECHSPEC High Performance Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
