

## 254.0mm/10.0" Optic Dia., Optical Cell Kinematic Mount



Stock #36-478 [CONTACT US](#)

- 1 + £3,504<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	£3,504.00 each
Qty 5+	£3,264.72 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Adjustable - Tip-Tilt

Type:

Circular

Type of Optics:

7°

Range:

10.06	<b>Inner Diameter (inches):</b>
	<b>Optic Holding Style:</b> Three Spring-Loaded Clips
<b>Physical &amp; Mechanical Properties</b>	
9.58	<b>Clear Aperture CA (inches):</b>
243.3	<b>Clear Aperture CA (mm):</b>
203.2	<b>Optical Centerline (mm):</b>
16.00 x 8.00 x 15.00	<b>Dimensions (inches):</b>
406.4 x 203.2 x 381.0	<b>Dimensions (mm):</b>
52.0	<b>Weight (lbs):</b>
	<b>Construction:</b> Black Anodized Aluminum, Stainless Steel
10.00	<b>Diameter of Compatible Optics (inches):</b>
8.00	<b>Optical Centerline (inches):</b>
43.5	<b>Max. Thickness of Compatible Optics (mm):</b>
0.031	<b>Adjustment Screw Pitch (inches):</b>

<b>Threading &amp; Mounting</b>	
254.0	<b>Size of Compatible Optics (mm):</b>

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- Robust Kinematic Mounts for Larger Diameter Optics
- Ball Pivot and Fine Pitch Screws Provide Pitch and Roll
- 50% Greater Resolution than Micrometer Adjustments

Optical Cell Kinematic Mounts provide highly stable kinematic movement with two axis tilt (pitch and roll) provided by a precise ball pivot adjustment and an orthogonal three-point suspension. Adjustment is made by three 64-pitch screws (two 64-pitch screws for 1-2" diameter model). For the 6" diameter model, adjustment is made by two 64-pitch screws for and with three 32-pitch screws for 8" up to 12.5" diameter models. Optical Cell Kinematic Mounts feature fine pitch screws, which permit 50% greater resolution than a micrometer. An angled base on the mount allows for stand-alone installation and mounting. These mounts have integral optic cell design allowing optics to be held undistorted.

**Note:** For mounting 12" diameter optics in our 12.5" Diameter Optical Mount, use the 12.5" to 12" Adapter Kit (#12-226). The Adapter Kit and 12.5" Diameter Optical Mount are offered together as #12-227.

## Technical Information

Optic Diameter	A	B	C	D	E	F	G	H	I	J	K	Stock No.
1-2"	2.25-20 TPI	3.75	2.00	2.00	0.38	2.00	3.50	0.28	-	2.12	-	<a href="#">#53-964</a>
3"	3.25-20 TPI	5.75	3.00	4.00	1.25	3.38	6.25	0.28	-	5.00	-	<a href="#">#53-965</a>
4.25"	4.625-20 TPI	5.75	3.00	4.00	1.25	3.38	6.25	0.28	-	5.00	-	<a href="#">#57-872</a>

Optic Diameter	A	B	C	D	E	F	G	H	I	J	K	Stock No.
6"	6.187-32 TPI	8.00	6.00	5.00	5.00	4.50	8.00	0.28	5.75	6.00	1.19	<a href="#">#36-474</a>
8"	8.06	12.00	7.00	10.00	6.00	6.25	11.50	0.28	7.62	9.00	1.60	<a href="#">#36-476</a>
10"	10.06	16.00	8.00	12.00	6.00	8.00	15.00	0.53	9.58	12.50	1.75	<a href="#">#36-478</a>
12.5"	12.56	16.00	8.00	12.00	6.00	8.00	15.00	0.53	12.08	12.50	2.13	<a href="#">#36-480</a>

