

TECHSPEC[®] 100mm Focal Length, LF Series Fixed Focal Length Lens



100mm Focal Length, #85-204

Stock **#85-204** 3-4 DAYS



1



£1,275.00

ADD TO CART

Qty 1+

£1,275.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
104.00

Horizontal Field of View, 1/2" Sensor:
29.2mm - 3.7°

Horizontal Field of View, 2/3" Sensor:
40.1mm - 5.0°

Filter Thread:

M46 x0.75 (Female)
Maximum Diameter (mm): 61
Weight (g): 564
Horizontal Field of View, 1/3" Sensor: 21.9mm - 2.7°
Maximum Rear Protrusion (mm): 0
Horizontal Field of View, 1" Sensor: 58.4mm - 7.3°
Maximum Image Circle (mm): 43.30
Numerical Aperture NA, Object Side: 0.0318
Horizontal Field of View @ Max Sensor Format: 164.5mm - 20.3°
Horizontal Field of View, 35mm Sensor: 164.5mm - 20.3°
Horizontal Field of View, 4/3" Sensor: 102.2mm - 12.7°
Horizontal Field of View, 1.1" Sensor: 64.8mm - 8.1°
Number of Elements (Groups): 8 (5)
Horizontal Field of View, 1/1.8" Sensor: 32.8mm - 4.1°
Horizontal Field of View, 1/2.5" Sensor: 26.4mm - 3.3°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 100.00
Primary Magnification PMAQ: 0.22
Maximum Sensor Format: 35mm
Working Distance (mm): 500 - ∞
Mount: F-Mount
Aperture (f/#): f/2.8 - f/22
Coating: λ/4 MgF ₂
Coating Specification: λ/4 MgF ₂
Entrance Pupil Position (mm): 55.2
Horizontal Field of View, 1/4" Sensor: 16.4mm - 2.1°
Object Space Principal Plane (mm): 48.56
Image Space Principal Plane (mm): -51.39
Field of View at Max Sensor Format: Horizontal: 158.2mm - 19.7° Vertical: 118.6mm - 14.8° Diagonal: 198.1mm - 24.5°
Maximum Distortion (%): 0.06
Horizontal Field of View, APS-H Sensor: 133.3mm - 16.6°
Horizontal Field of View, APS-C Sensor: 102.2mm - 12.7°
Exit Pupil Position (mm): -45.16
Lens Wavelength Range: VIS
Imaging Lens Type: Lens for Large Format Sensors
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)
