

[See all 6 Products in Family](#)

100X Water Immersion Objective, Nikon CFI60 Plan

See More by [Nikon](#)



Stock #75-360 NEW 1 In Stock

-

1

+

£11,448⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£11,448.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
MRL07920	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm	
Microscope Objective	Type:
Infinity Corrected	Style:

Nikon	Manufacturer:
Physical & Mechanical Properties	
0.22	Field of View (mm):
57.30	Length excluding Threads (mm):
35.5	Maximum Diameter (mm):
225	Weight (g):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
0.064	Horizontal Field of View, 1/2" Sensor:
0.088	Horizontal Field of View, 2/3" Sensor:
100X	Magnification:
1.10	Numerical Aperture NA:
2.5	Working Distance (mm):
22	Field Number (mm):
60.5	Parfocal Length (mm):
Water	Immersion Liquid:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
M25 x0.75	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Water Dipping Design for Live Imaging
- Optimized for Infrared (IR) and Multiphoton Microscopy
- High NA for Superior Resolution

Nikon CFI60 Water Dipping Objectives design allows direct immersion into aqueous samples, reducing optical aberrations and enabling high-resolution, live imaging of thick specimens. These objectives are designed with high numerical apertures and long working distances and are available in a variety of magnifications. Featuring M25 x0.75 mounting threads, these objectives can be easily integrated into existing microscopy systems. Nikon CFI60 Water Dipping Objectives enable high-resolution, low-aberration imaging deep within living tissues by efficiently transmitting infrared light and correcting optical distortions specific to multiphoton and IR microscopy.