

TECHSPEC® 10° Nom. 12.5mm Dia. VIS-NIR, N-BK7 Wedge Prism



Stock #35-800 3-4 DAYS

1 £42.50

ADD TO CART

Qty 1-5
£42.50

Qty 6+
£34.00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
VIS-NIR (400-1000nm)

Angle Tolerance (arcsec):
±30

Bevel:
Protective bevel as needed

Coating Specification: R_{abs} ≤0.25% @ 880nm R_{avg} ≤1.25% @ 400 - 870nm R_{avg} ≤1.25% @ 890 - 1000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 12.50 +0.00/-0.10
Edge Thickness ET (mm): 1.5
Image Orientation: Beam Deviation
Power (diopters): 17.63
Ray Deviation @ 633nm (°): 10.00
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Type: Wedge Prism
Wavelength Range (nm): 400 - 1000
Wedge Angle: 18° 8'

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant