

TECHSPEC[®] 10° Nom. VIS 0° Coated, N-BK7 Wedge Prism



Stock #49-444 3-4 DAYS

-

1

+

£48.88

ADD TO CART

Qty 1-5
£48.88
Qty 6+
£39.10
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
VIS 0° (425-675nm)

Angle Tolerance (arcsec):
±30

Bevel:
Protective bevel as needed

Coating Specification: R_{avg} ≤ 0.4% @ 425 - 675nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 25.00 +0.00/-0.10
Image Orientation: Beam Deviation
Power (diopters): 17.63
Ray Deviation @ 633nm (°): 10.00
Substrate: N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 3.00
Type: Wedge Prism
Wavelength Range (nm): 425 - 675
Wedge Angle: 18° 8'
Maximum Edge Thickness (mm): 11.2
Damage Threshold, Reference: 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant