

10.6µm CWL, 25.0mm Diameter, 1.5 FWHM, IR Bandpass Filter



Stock **#33-145** 3-4 DAYS

[Additional Bandwidths](#)



1



£693.60

ADD TO CART

Qty 1-9

£693.60

Qty 10+

£658.92

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm): 21.0
Center Wavelength CWL (nm): 10,600.00 ±10
Full Width-Half Max FWHM (nm): 1,500.00
Substrate: □ Germanium (Ge)
Coating: Traditional Coated
Surface Quality: 60-40
Thickness (mm): 1.00 ±0.2
Transmission (%): 80 (minimum)
Type: Bandpass Filter
Typical Applications: Carbon Dioxide Emission
Blocking Wavelength Range (nm): 200 - 16500
Center Wavelength CWL (μm): 10.60 ±0.01
Full Width-Half Max FWHM (μm): 1.50 ±0.01

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant