

TECHSPEC® 10mm 266nm, Laser Line λ /20 High Tolerance Right Angle Mirror



Stock **#37-641** 3-4 DAYS

- 1 + **£197.20**

ADD TO CART

Qty 1-5
£197.20

Qty 6+
£157.67

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 λ /20

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Length of Legs (mm): 10.00
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R _{abs} >99.5% @ 266nm @ 45° AOI R _{avg} >99.5% @ 263 - 268nm @ 45° AOI
Coating: Laser Mirror (266nm)
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Design Wavelength DWL (nm): 266
Length of Hypotenuse (mm): 14.10
Type: Right Angle Mirror
Pyramid Tolerance (arcmin): ±1
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference: ☐ 1MW/cm ² @ 266nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View