

TECHSPEC® 10mm 355nm, Laser Line $\lambda/20$ High Tolerance Right Angle Mirror



Stock **#37-647** **1 In Stock**

£210⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£210.40 each
Qty 6-25	£168.80 each
Qty 26-49	£158.40 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Right Angle Mirror **Type:**

Physical & Mechanical Properties

Protective as needed **Bevel:**

90 **Clear Aperture (%):**

+0.00/-0.10	Dimensional Tolerance (mm):
14.10	Length of Hypotenuse (mm):
10.00	Length of Legs (mm):

Optical Properties

Laser Mirror (355nm)	Coating:
$\lambda/20$	Surface Flatness (P-V):
355	Design Wavelength DWL (nm):
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
$R_{\text{abs}} > 99.8\%$ @ 355nm @ 45° AOI $R_{\text{avg}} > 99.5\%$ @ 351 - 358nm @ 45° AOI	Coating Specification:
20-10	Surface Quality:
1MW/cm ² @ 355nm	Damage Threshold, Reference: <input type="checkbox"/>
±1	Pyramid Tolerance (arcmin):
±15	Angle Tolerance (arcsec):

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- >99.5% Reflectivity at the Design Wavelength
- ±15 Arcsecond Angular Tolerance
- High Thermal Stability Substrates

TECHSPEC® Laser Line $\lambda/20$ High Tolerance Right Angle Mirrors are designed at Nd:YAG wavelengths with durable, high reflectivity dielectric coatings. Right angle mirrors are easily mounted and integrated into systems that redirect light 90°. With ±15 arcsecond angular tolerance and ±1 arcminute pyramid tolerance, these laser line mirrors simplify alignment when mounting. TECHSPEC® Laser Line $\lambda/20$ High Tolerance Right Angle Mirrors feature laser induced damage threshold specifications making them ideal for demanding laser applications.

