

**TECHSPEC® 12.5mm Dia.  $\lambda/10$  ZERODUR® Uncoated Mirror Substrate**



Stock #71-507 **1 In Stock**

⊖ 1 ⊕ £64<sup>40</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	£64.40 each
Qty 6-25	£51.52 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Mirror Substrate **Type:**

**Physical & Mechanical Properties**

12.50 +0.00/-0.20 **Diameter (mm):**

3.00 ±0.20 **Thickness (mm):**

Commercial Polish	<b>Back Surface:</b>
Protective as needed	<b>Bevel:</b>
90	<b>Clear Aperture (%):</b>
Ground	<b>Edges:</b>
30	<b>Parallelism (arcsec):</b>

## Optical Properties

Uncoated	<b>Coating:</b>
$\lambda/10$	<b>Surface Flatness (P-V):</b>
ZERODUR®	<b>Substrate:</b> <input type="checkbox"/>
20-10	<b>Surface Quality:</b>

## Material Properties

0.1	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
-----	---

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- Precision ZERODUR® Substrates
- $\lambda/10$  Flatness
- Low Coefficient of Thermal Expansion

TECHSPEC® ZERODUR Mirror Substrates are well suited for applications where temperature fluctuation is a concern. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of  $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$ , which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront, even when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® ZERODUR Mirror Substrates feature precision polished substrates with  $\lambda/10$  flatness and 20-10 surface quality.