

10X (13 - 130mm FL) C-Mount, Close Focus Zoom Lens



10X (13 - 130mm FL) C-Mount, Close Focus Zoom Lens, #54-363

Stock **#54-363** [CONTACT US](#)

⊖ 1 ⊕ £616⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£616.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Minimum: 0.82X - 0.085X
Maximum: 0.23X - 0.023X

Note:

Macro Zoom Lens

Type:

Physical & Mechanical Properties

98.50

Length (mm):

48.00 **Maximum Diameter (mm):**

233.00 **Weight (g):**

Optical Properties

7.8 - 280mm **Horizontal Field of View, 1/2" Sensor:**

10:1 **Zoom Ratio:**

13-130 **Focal Length Range (mm):**

0.82X - 0.023X **Primary Magnification PMAG:**

152 - 457 **Working Distance (mm):**

f/5.6 - f/32 **Aperture (f/#):**

VIS **Lens Wavelength Range:**

Sensor

1/2" **Maximum Sensor Format:**

Threading & Mounting

M46 x 0.75 **Filter Thread:**

C-Mount **Mount:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[Contains SVHC\(s\)](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

Product Details

- Large Zoom
- Close Focus Capability
- Broad Field of View Range

Close Focus Zoom Lenses are ideal for multipurpose applications that need both close focus and wide fields of view. The lenses offer variable apertures, to adjust the depth of field. Filter threading allows the use of filters to adjust incoming light levels with ND filters, or increase contrast with color filters on monochrome sensors, and more. Close Focus Zoom Lenses are economical and compact, and these lenses have many features that make them a perfect choice for a variety of uses. These zoom lenses feature 10X magnification and are compatible with C-mounts.

Note: #58-240 Close Focus Zoom Lens can be used for working distances from 127mm to infinity, where its field of view would be 8 - 48mm (horizontal for 2/3" sensors) at minimum working distance.

Technical Information

