


11 x 11mm, 600 - 1100nm, Corning Polarcor™ Glass Polarizer



Corning Polarcor™ Glass Polarizers

Stock #13-627 3-4 DAYS



1



£722.50

ADD TO CART

Qty 1+

£722.50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0 ±5

Coating:
BBAR (600-1100nm)

Extinction Ratio:
>10,000:1

Substrate: ☐
Borosilicate Glass Containing Elongated Silver
Crystals

Length (mm): 11.00
Minimum Transmission (%): >66
Dimensions (mm): 11.0 x 11.0
Surface Quality: 40-20
Thickness (mm): 0.50 ±0.05
Dimensional Tolerance (mm): ±0.1
Coating Specification: R_{avg} <1.0% @ 600 - 1100nm
Wavelength Range (nm): 600 - 1100
Width (mm): 11.00
Insertion Loss (dB): <1.8
Index of Refraction n_d: 1.5218-1.5107
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 6.5
Knoop Hardness (kg/mm²): 480
Young's Modulus (GPa): 58.605
Poisson's Ratio: 0.21
Abbe Number (v_d): 57.6
Density (g/cm³): 2.412

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View