

[See all 7 Products in Family](#)

TECHSPEC®

10X, 0.18 NA, UCf Objective



Stock #26-688 12 In Stock

-

1

+

£193⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-2	£193.60 each
Qty 3-4	£180.80 each
Qty 5-9	£174.40 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fluorite	Type:
Finite Conjugate	Style:
Manufacturer:	

Edmund Optics®	
Physical & Mechanical Properties	
78.75	Length (mm):
29	Maximum Diameter (mm):
67	Weight (g):
Optical Properties	
0.88	Horizontal Field of View, 2/3" Sensor:
1.408	Horizontal Field of View, 1.1" Sensor:
8.00	Focal Length FL (mm):
10X	Magnification:
0.18	Numerical Aperture NA:
3.70	Resolving Power (µm):
8.29	Depth of Field (µm):
8.1	Working Distance (mm):
400 - 700	Wavelength Range (nm):
17.6	Field Number (mm):
Sensor	
1.1"	Maximum Sensor Format:
Threading & Mounting	
C-Mount	Mounting Threads:
Environmental & Durability Factors	
+10 to +40	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Compact Finite Conjugate Objectives
 - Mount Directly to a C-Mount Camera
 - Near Diffraction Limited performance
- TECHSPEC® UCf Objective Series are compact objectives that are finite conjugate by design, but achieve similar imaging performance of infinity corrected objectives and do not require a secondary tube lens to generate an image on the sensor. Available at 2X, 4X, 5X, 10X, 15X, and 20X magnifications. These objectives mount directly to a C-mount camera without additional extension tubes.