

TECHSPEC® 116mm Dia x 1524.7mm FL Achromatic Lens, Mtd



Stock #54-568 4 In Stock

-

1

+

£1,192^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	£1,192.00 each
Qty 6-25	£1,012.00 each
Qty 26-49	£952.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens

Type:

Physical & Mechanical Properties

116.00 +0.00/-0.12

Diameter (mm):

98.00

Clear Aperture CA (mm):

5.00	Centering (arcmin):
12.37	Center Thickness CT 1 (mm):
8.76	Center Thickness CT 2 (mm):
-2169.77	Radius R ₄ (mm):
23.35	Edge Thickness ET (mm):
Mounted, Airspaced 0.10mm	Construction:
Protective as needed	Bevel:

Optical Properties

1,524.73	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
1514.53	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
908.13	Radius R ₁ (mm):
-626.59	Radius R ₂ (mm):
-625.40	Radius R ₃ (mm):
N-BK7 / N-SF2	Substrate:
60-40	Surface Quality:
14.9	f/#:
0.03	Numerical Aperture NA:
MgF ₂ (400-700nm)	Coating:
R _{avg} ≤1.75% @ 400 - 700nm	Coating Specification:
400 - 700	Wavelength Range (nm):

Threading & Mounting

28.35	Mount Thickness (mm):
M12 x 1.0	Mounting Threads:

Regulatory Compliance


View	Certificate of Conformance:
----------------------	-----------------------------

Product Details


- Offered in Cemented or Air-Spaced Designs
- Mounted Versions Available for Easy Integration
- Feature MgF₂ Anti-Reflection Coating

TECHSPEC® Large Precision Achromatic Lenses offer near-diffraction limited performance across the designated wavelength range. These color-corrected achromatic lenses feature long focal lengths and are available in either cemented or air-spaced designs. The lenses have a MgF₂ anti-reflection coating and are available in diameters up to 140mm. TECHSPEC® Large Precision Achromatic Lenses, in the mounted version, feature a male mounting thread for easy integration into optical systems. Adhesive foil spacers and mounting instructions are included for unmounted, air-spaced achromatic lenses.

Technical Information



Airspaced



Coating Curves