

12 x 12mm, 500µm Pitch, 6° Div., Double Cyl. Lens Array VIS-NIR



Stock #72-595 **1 In Stock**

⊖ 1 ⊕ £765⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£765.00 each
Qty 11+	£610.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Array

Type:

Physical & Mechanical Properties

12.0 x 12.0 ±0.10

Dimensions (mm):

2.150

Radius R (mm):

2.00 ±0.10 **Thickness (mm):**

Optical Properties

Effective Focal Length EFL (mm):
4.78 @ 1064nm

Substrate:
[Fused Silica](#) (Corning 7980)

Coating:
VIS-NIR (400-1000nm)

Wavelength Range (nm):
400 - 1000

Coating Specification:
R_{abs} ≤ 0.25% @ 880nm @ 0° AOI
R_{avg} ≤ 1.25% @ 400 - 870nm @ 0° AOI
R_{avg} ≤ 1.25% @ 890 - 1000nm @ 0° AOI

Divergence Angle (°):
6.0 (Full Width)

Pitch (µm):
500.00

Array Type:
Double-Sided (with cross-oriented lenses)

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.

Coating Curves