

## 120 MHz Fiber Coupled Optical Receiver Module



Stock #87-324 CLEARANCE **5 In Stock**

- 1 + £146<sup>.36</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£146.36 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Optical Properties

1310 - 1550 **Wavelength Range (nm):**

50/125/245/900 **Fiber Diameter (µm):**

### Sensor

25.00 **Dynamic Range (dB):**

### Electrical

## Hardware & Interface Connectivity

FC/PC

Connector:

## Regulatory Compliance

[View](#)


Certificate of Conformance:

## Product Details

- High Sensitivity and Overload Power with Wide Dynamic Range
- Designed for Bandwidths of 3MHz and 120MHz and Wavelength Ranges of 1310 – 1550nm
- Ideal for Biomedical, Industrial, or Telecommunication Optical Sensor Systems

Fiber-Coupled Optical Receiver Modules are ideal for use in biomedical optical sensor systems or for industrial and telecommunication sensing applications. Fiber-Coupled Optical Receiver Modules feature high sensitivity and high overload power, in addition to wide dynamic ranges. These receiver modules are designed for use in common telecommunication wavelength ranges.

## Technical Information



Pin	Function
1	-5V detector bias
2, 6, 9, 11	No connection
12, 13, 14	No connection
3, 5, 8	Ground
4	-5V (LDFR = NC)
7	Output
10	+5V