

12 x 12mm, 500µm Pitch, 3.7° Divergence, Cyl. Microlens Array



Stock #23-870 3-4 DAYS

-

1

+

£454.75

ADD TO CART

Qty 1-10
£454.75
Qty 11+
£409.70
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
7.78 @ 1064nm

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:

Lens Array (One Sided)
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.1
Dimensions (mm): 12.0 x 12.0
Divergence Angle (°): 3.7 (Full Width)
Pitch (µm): 500
Radius R (mm): 3.500
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View