

[See all 102 Products in Family](#)

TECHSPEC<sup>®</sup> 12.0mm Diameter x 48.0mm FL, 785nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock **#65-522** 20+ In Stock

☐ [Other Coating Options](#)

-

1

+

£42<sup>40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | £42.40 each                   |
| Qty 10-25      | £38.20 each                   |
| Qty 26-49      | £33.80 each                   |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

|                                  |                                                       |
|----------------------------------|-------------------------------------------------------|
| Plano-Convex Lens                |                                                       |
| Physical & Mechanical Properties |                                                       |
| 12.00 +0.0/-0.025                | Diameter (mm):                                        |
| <1                               | Centering (arcmin):                                   |
| 2.50 ±0.05                       | Center Thickness CT (mm):                             |
| 1.76                             | Edge Thickness ET (mm):                               |
| 11                               | Clear Aperture CA (mm):                               |
| Protective as needed             | Bevel:                                                |
| Optical Properties               |                                                       |
| 48.00 @ 587.6nm                  | Effective Focal Length EFL (mm):                      |
| 46.36                            | Back Focal Length BFL (mm):                           |
| Laser V-Coat (785nm)             | Coating:                                              |
| R <sub>abs</sub> <0.25% @ 785nm  | Coating Specification:                                |
| N-BK7                            | Substrate: <input type="checkbox"/>                   |
| 40-20                            | Surface Quality:                                      |
| 1.5λ                             | Power (P-V) @ 632.8nm:                                |
| λ/4                              | Irregularity (P-V) @ 632.8nm:                         |
| ±1                               | Focal Length Tolerance (%):                           |
| 24.82                            | Radius R <sub>1</sub> (mm):                           |
| 4.00                             | f/#:                                                  |
| 0.13                             | Numerical Aperture NA:                                |
| 785                              | Design Wavelength DWL (nm):                           |
| 5 J/cm² @ 785nm, 10ns            | Damage Threshold, By Design: <input type="checkbox"/> |
| Regulatory Compliance            |                                                       |
| Compliant                        | RoHS 2015:                                            |
| View                             | Certificate of Conformance:                           |
| Compliant                        | Reach 235:                                            |

## PRODUCT DETAILS

- <0.25% Reflection at 785nm
- BBAR Coating Options Also Available: [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- [405nm](#), [532nm](#), [633nm](#), 785nm, [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® 785nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 785nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#), [532nm](#), [633nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

## TECHNICAL INFORMATION



## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## COMPATIBLE MOUNTS