

TECHSPEC® 12.5/12.7mm Diameter, T-Mount Thin Optic Mount



Stock #52-933 **5 In Stock**

- 1 + £57.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£57.60 each
Qty 5-9	£54.24 each
Qty 10-25	£51.84 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fixed **Type:**

Optic Mount (Fixed) **Function:**

Type of Optics:

Physical & Mechanical Properties

11.5 **Extension Length (mm):**

14.95 **Total Length (mm):**

2.00 **Min. Thickness of Compatible Optics (mm):**

5.50 **Max. Thickness of Compatible Optics (mm):**

11.50 **Clear Aperture CA (mm):**

Black Anodized Aluminum (6061 T6) **Construction:**

48.0 **Outer Diameter (mm):**

Threading & Mounting

T-Mount **Thread Type:**

12.5 - 12.7 **Diameter of Compatible Optics (mm):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **REACH 241:**

Product Details

This stock number is a 3-part design.

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x32TPI, M12 x0.5, or M42 x0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

Note: #56-353, #56-354, #52-933, and #52-292 are all 3-part assemblies

Technical Information

