

TECHSPEC®

12.5 x 25mm, 0.33 Numerical Aperture, Uncoated, Truncated Precision Aspheric Lens



Stock #17-313 CLEARANCE 3-4 DAYS

- 1 + **£276.25**

ADD TO CART

Qty 1-5
£276.25

Qty 6+
£221.00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
12.50 x 25.00

Effective Focal Length EFL (mm):
37.50 @ 587.6nm

Numerical Aperture NA:
0.33

Back Focal Length BFL (mm): 31.09
Substrate:  N-BK7
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 10.50 x23.00
Edge Thickness ET (mm): 5.49
Center Thickness CT (mm): 9.72 ±0.10
f/#: 1.50
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Conjugate Distance: Infinite
Power (diopters): 26.67

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View