

TECHSPEC® 12.5mm Dia 1480nm 0°, Laser Diode Mirror



Stock **#63-132** CLEARANCE ☐ **In Stock**

-

1

+

£33.96

ADD TO CART

Qty 1+
£33.96

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality: 10-5
Type: Laser Mirror
Parallelism (arcmin): <3
Clear Aperture (%): >90

Back Surface: Ground
Reflection at DWL (%): 99.8
Coating Specification: R _{abs} >99.8% @ 1480nm R _{avg} >98% @ 1376 - 1584nm
Wavelength Range (nm): 1346 - 1584
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Dielectric Mirror (1376-1584nm)
Design Wavelength DWL (nm): 1480
Diameter (mm): 12.50 +0.0/-0.2
Thickness (mm): 6.00 ±0.2
Angle of Incidence (°): 0
Substrate: ☐ Fused Silica (Corning 7980)

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View