

TECHSPEC[®] 12.5mm Dia. 0.5° Nom. Fused Silica Wedge Prism 532nm Laser V-Coat



TECHSPEC Fused Silica Wedge Prisms

Stock **#39-089** CLEARANCE 3-4 DAYS

⊖

1

⊕

£80.71

ADD TO CART

Qty 1+

£80.71

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Laser V-Coat (532nm)

Angle Tolerance (arcsec):
30

Bevel:
Protective bevel as needed

Coating Specification:
R_{abs} <0.25% @ 532nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52
Design Wavelength DWL (nm): 532
Diameter (mm): 12.50
Image Orientation: Beam Deviation
Power (diopters): 0.87
Ray Deviation @ 355nm (°): 0.50
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Wedge Angle: 1° 3'0"
Note: Specificy this is S1 & S2 power and irregularity, not the overall power of the wedge
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 20ns, 20Hz
Power (fringes) @ 632.8nm: 0.50
Irregularity (fringes) @ 632.8nm: 0.20

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View