

TECHSPEC[®] 12.5mm Dia. x 12.5mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock #65-550 ☒ In Stock



1



£92.65

ADD TO CART

Qty 1-5

£92.65

Qty 6+

£74.16

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):

12.50
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 7.23
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.50
Centering (arcmin) : <1
Center Thickness CT (mm) : 10.62 ±0.10
Center Thickness CT 1 (mm) : 8.12 ±0.05
Center Thickness CT 2 (mm) : 2.50 ±0.05
Radius R₁ (mm) : 9.53
Radius R₂ (mm) : -6.92
Radius R₃ (mm) : -20.07
Edge Thickness ET (mm) : 7.29
Substrate: ☐ N-BASF64 / N-SF66
Surface Quality : 40-20
f/# : 1.00
Numerical Aperture NA : 0.50
Coating : MgF ₂ (400-700nm)
Coating Specification : R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View