

TECHSPEC® 12.5mm Dia. x 17.5mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#49-940-INK** ☒ In Stock
[Other Coating Options](#)

1 **£77.35**

ADD TO CART

Qty 1-5
£77.35
Qty 6+
£61.84
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 ±0.025

Effective Focal Length EFL (mm):

17.50
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 13.59
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 7.30 ±0.10
Center Thickness CT 1 (mm): 5.80 ±0.05
Center Thickness CT 2 (mm): 1.50 ±0.05
Radius R ₁ (mm): 12.20
Radius R ₂ (mm): -9.82
Radius R ₃ (mm): -39.19
Edge Thickness ET (mm): 5.08
Substrate: ☐ N-BAF10 / N-SF57
Surface Quality: 40-20
f/#: 1.4
Numerical Aperture NA: 0.36
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View