

[See all 68 Products in Family](#)

TECHSPEC® 12.5mm Diameter MgF₂ Coated, B270 Window

See More by [SCHOTT Optical Components](#)



Stock #32-948 **4 In Stock**

£33²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£33.20 each
Qty 6-25	£27.20 each
Qty 26-99	£24.80 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window **Type:**
Glass **Type of Window:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

11.25	Diameter (mm):
12.50 ±0.25	
	Thickness (mm):
2.00	
	Dimensional Tolerance (mm):
±0.25	
	Bevel:
Protective as needed	
	Edges:
Fine Ground	
	Poisson's Ratio:
0.22	
	Young's Modulus (GPa):
71.5	
	Knoop Hardness (kg/mm²):
500.00	

Optical Properties

	Coating:
MgF ₂ (632.8nm)	
	Substrate: <input type="checkbox"/>
B270	
	Index of Refraction (n_d):
1.523	
	Surface Quality:
60-40	
	Abbe Number (v_d):
58.3	
	Coating Specification:
R _{avg} ≤1.50% @ 632.8nm (N-BK7)	
	Wavelength Range (nm):
400 - 700	
	Surface Flatness (P-V):
1λ	
	Damage Threshold, By Design: <input type="checkbox"/>
10 J/cm ² @ 532nm, 10ns	

Material Properties

	Density (g/cm³):
2.56	
	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
9.4 (+20 to +300°C)	

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Large Selection of Sizes
- Available Uncoated, MgF₂, or VIS-NIR Anti-Reflection (AR) Coated
- Custom Sizes Available for Volume OEM Requirements

TECHSPEC® B270 Windows offer a high transmission from the visible to the near-infrared (NIR). They have a similar refractive index to N-BK7 while being more cost-effective. These windows are often used as a protective element due to their high solarization stability and chemical resistance, making them ideal for standard window applications. TECHSPEC® B270 Windows are available either uncoated or coated with a MgF₂ or VIS-NIR Anti-Reflection (AR) Coating. Both circular and square options are offered in various sizes, and custom sizes and coatings are available for OEM applications.

Technical Information



Compatible Mounts
