

TECHSPEC®

12.5mm H x 25mm L x 20mm FL VIS-NIR Coated, Illumination Grade PCX Cylinder Lens



Stock #69-773 3-4 DAYS

- 1 + **£69.70**

ADD TO CART

Qty 1-5
£69.70

Qty 6+
£55.67

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
20.00

Substrate: ☐
[N-BK7](#)

f#:

1.6
Numerical Aperture NA: 0.31
Coating: VIS-NIR (400-1000nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): 17.63
Center Thickness CT (mm): 3.60
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 1.50
Focal Length Tolerance (%): ±3
Radius R ₁ (mm): 10.34
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant