


## TECHSPEC® 127 x 127mm, Enhanced Aluminum, 4-6λ Mirror



Stock #18-934 3-4 DAYS

⊖ 1 ⊕ **£59.07**

**ADD TO CART**

Qty 1-5

£59.07

Qty 6+

£46.75

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Surface Flatness (P-V):**  
4 - 6λ

**Substrate:**   
Float Glass

**Surface Quality:**  
60-40

**Dimensions (mm):**  
127.00 x 127.00 +0.00/-0.25

**Coating Specification:**  
R<sub>avg</sub> ≥95% @450 - 650nm @45°

**Coating:**  
Enhanced Aluminum (450-650nm)

**Coating Type:**  
Metal

**Clear Aperture CA (mm):**  
114.30 x 114.30

**Edges:**  
Seamed, 0.5mm Maximum Edge Chip

**Thickness (mm):**  
3.00 (nominal)

**Type:**  
Flat Mirror

**Wavelength Range (nm):**  
450 - 650

**Length (mm):**  
127.00

**Width (mm):**  
127.00

**Damage Threshold, By Design:**   
0.2 J/cm<sup>2</sup> @532nm, 10ns

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**REACH 241:**  
[Compliant](#)

---