

12.7mm Dia., 355nm, $\lambda/2$ High Energy Waveplate



High Energy Quartz Waveplates

Stock **#25-447** **3 In Stock**

-

1

+

£399²⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£399.20 each
Qty 11+	£328.80 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

High Energy Waveplate

Physical & Mechanical Properties

Clear Aperture CA (mm):

8.0

Diameter (mm):

12.70

+0/-0.2		Dimensional Tolerance (mm):
Optically Bonded on UVFS (C7980) Substrate		Construction:
<3		Parallelism (arcsec):
Optical Properties		
R _{avg} <0.3%		Coating:
355		Design Wavelength DWL (nm):
Crystalline Quartz		Substrate: ☐
λ/2		Retardance:
20-10		Surface Quality:
<λ/10 @ 632.8nm		Transmitted Wavefront, P-V:
λ/180 @ 20°C		Retardance Tolerance:
>20 J/cm² @ 1064nm, 10ns, 10Hz		Damage Threshold, By Design: ☐
1		Retardance Order:
Threading & Mounting		
6 ±0.2		Mount Thickness (mm):
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		Reach 247:

Product Details

- Damage Threshold up to >20 J/cm² @ 1064nm
 - λ/4 and λ/2 Retardance
 - Black Anodized Aluminum Mount
 - UV to NIR Design Wavelengths Available
- High Energy Quartz Waveplates are available in both λ/4 and λ/2 retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to >20 J/cm² at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.