

[See all 1 Products in Family](#)

## 12.7mm Dia. UHR Broadband Dielectric Mirror, 400-750nm



Stock #17-500 **CLEARANCE** 20+ In Stock

⊖ 1 ⊕ £187.<sup>96</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£187.96 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Flat Mirror **Type:**

### Physical & Mechanical Properties

12.70 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.20 **Thickness (mm):**

11.7 **Clear Aperture CA (mm):**

Ground Edges:

Parallelism (arcmin):  
<3

## Optical Properties

Dielectric Coating Type:

UHR Dielectric Mirror (400-750nm) Coating:

$\lambda/10$  Surface Flatness (P-V):

400 - 750 Wavelength Range (nm):

Fused Silica (Corning 7980) Substrate:

45 Angle of Incidence (°):

Coating Specification:  
 $R_{avg} > 99.9\%$  @ 400 - 750nm (45°, s-pol)  
 $R_{avg} > 99.8\%$  @ 410 - 750nm (45°, p-pol)

10-5 Surface Quality:

## Regulatory Compliance

View Certificate of Conformance:

## Product Details

- >99.8% Reflectivity over Broad Visible or NIR Wavelength Ranges
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- $\lambda/10$  Surface Flatness

Ultra-High Reflectivity (UHR) Broadband Dielectric Mirrors are ideal for use with broadband [laser](#) or [illumination](#) sources in applications that require low reflection loss. These mirrors feature laser grade substrates with  $\lambda/10$  surface flatness and 10-5 surface quality to minimize scattering effects. Coated with durable dielectric coatings, these mirrors are designed for >99.8% average reflectivity throughout the visible (400 - 750nm) or NIR (740 - 1100nm) spectra, independent of polarization. With a high-quality fused silica substrate, Ultra-High Reflectivity (UHR) Broadband Dielectric Mirrors feature a low coefficient of thermal expansion.

**Coating Note:** Coating designs measured and verified at 532, 632.8, and 1064nm via cavity ring-down spectroscopy (CRDS). Specs may not be verifiable on traditional spectrophotometer equipment.

## Technical Information

