

TECHSPEC[®] 12.7mm Dia. x 12.7mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#49-854** 3-4 DAYS
[Other Coating Options](#)

-

1

+

£29.75

ADD TO CART

Qty 1-9
£29.75
Qty 10+
£26.77
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):

12.70 @ 587.6nm
Back Focal Length BFL (mm): 10.46
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 1.72
Radius R₁ (mm): 9.97
Clear Aperture CA (mm): 11.7
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant