

TECHSPEC[®] 12.7mm Dia. x 25.4mm FL, NIR II, Inked, Plano-Convex Lens



Stock **#67-510-INK** 3-4 DAYS
[Other Coating Options](#)

-

1

+

£42.92

ADD TO CART

Qty 1-9
£42.92
Qty 10+
£38.67
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 ±0.025

Effective Focal Length EFL (mm):

25.40 @ 587.6nm
Back Focal Length BFL (mm): 23.43
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.36
Radius R₁ (mm): 13.13
Clear Aperture CA (mm): 11.7
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View