


TECHSPEC[®] 12.7mm Dia x 50mm FL, Uncoated Imaging Grade PCX Cylinder Lens



Stock **#34-606** 20+ In Stock

-

1

+

£78⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£78.00 each
Qty 6-25	£70.00 each
Qty 26-49	£67.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Cylinder Lens, Plano-Convex

Physical & Mechanical Properties

Diameter (mm):


12.70 +0.0/-0.025	
Protective as needed	Bevel:
1.89	Center Thickness CT (mm):
±0.1	Center Thickness Tolerance (mm):
11.43	Clear Aperture CA (mm):
1.1	Edge Thickness ET (mm):
Optical Properties	
50.00	Effective Focal Length EFL (mm):
N-BK7	Substrate: ☐
6.00	f#:
0.13	Numerical Aperture NA:
Uncoated	Coating:
350 - 2200	Wavelength Range (nm):
48.75	Back Focal Length BFL (mm):
25.84	Radius R ₁ (mm):
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
<5	Plano Axis Wedge (arcmin):
<5	Power Axis Wedge (arcmin):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Ideal for Beam Shaping Applications
- Tightly Controlled Optical and Geometric Tolerances
- Rectangular and Circular Form Factors Available

TECHSPEC® Imaging Grade PCX Cylinder Lenses offer an ideal pairing of tightly controlled tolerances and scalable pricing for volume integration. As opposed to spherical lenses, which focus light in two dimensions, cylinder lenses are used to focus light in one dimension. AR Coating options are available for laser applications, minimizing stray light and maximizing throughput of a system. Our TECHSPEC Imaging Grade PCX Cylinder Lenses are specified to control geometric characteristics in order to ensure consistent performance from design to manufacturing. Typical applications include circularizing elliptical beams from a laser diode, creating a light sheet for measurement systems, or projecting a laser line onto a surface.

Note: For negative focal length cylinder lenses, see our [TECHSPEC Imaging Grade PCV Cylinder Lenses](#).



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).