

TECHSPEC[®] 12.7mm Silver and NIR II Coated, Mounted Corner Cube Retroreflector



Mounted N-BK7 Corner Cube Retroreflectors



Stock **#12-671** 20+ In Stock

-

1

+

£332⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£332.00 each
Qty 6-25	£265.60 each
Qty 26-49	£248.80 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Retroreflector

Physical & Mechanical Properties

+0.0/-0.1	Diameter Tolerance (mm):
12.70	Inner Diameter (mm):
31.75	Outer Diameter (mm):
Outer Diameter: +0/-0.5, Height: ±0.25	Housing Tolerance (mm):

Optical Properties

±5	Beam Deviation (arcsec):
NIR II & Silver with protective overcoat	Coating:
N-BK7	Substrate: ☐
60-40	Surface Quality:
Left-Handed	Image Orientation:
Reflective Surfaces: R _{abs} > 97% FROM400 - 2500nm @ 0° AOI R _{avg} > 98% FROM400 - 2500nm @ 0° AOI Entrance: R _{abs} ≤1.5% @ 750 - 800nm, R _{abs} ≤1.0% @ 800 - 1550nm, R _{avg} ≤0.7% @ 750 - 1550nm	Coating Specification:
180	Ray Deviation (°):
750 - 1550	Wavelength Range (nm):
0.25	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:

Threading & Mounting

(2) ¼-20 Tapped Holes	Mounting Threads:
-----------------------	-------------------

Regulatory Compliance

Not Compliant	RoHS 2015:
View	Certificate of Conformance:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Incident Light is Reflected Back to the Source
- Useful for Surveying and Alignment
- ¼-20 Tapped Holes for Easy Mounting
- Also Available [Unmounted](#)

TECHSPEC® Mounted N-BK7 Corner Cube Retroreflectors are mounted in an aluminum body and held in place with RTV potting cement. Due to their complex shape, corner cube retroreflectors can often be challenging to mount. These retroreflectors provide a convenient and durable solution. TECHSPEC® Mounted N-BK7 Corner Cube Retroreflectors are easily integrated via two ¼-20 tapped holes. In addition, each retroreflector has silvered reflecting surfaces to decrease polarization effects and increase field of view. For dimension details, see the "Technical Information" tab.

Corner cube retroreflectors are designed to reflect any ray or beam entering the prism face, regardless of the prism's orientation, back onto itself. A mirror will only do that at the normal angle of incidence. As a result, corner cube retroreflectors are ideal where precision alignment is difficult or time-consuming.



Technical Information

