

12mm Dia. x 12mm FL Protected Aluminum, Concave Mirror



Stock **#43-463** [CONTACT US](#)

-

1

+

£38^{.74}

ADD TO CART

Volume Pricing	
Qty 1-49	£38.74 each
Qty 50-99	£32.84 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Spherical Mirror

Physical & Mechanical Properties

12.00 ±0.50	Diameter (mm):
90	Clear Aperture (%):
3.0	Edge Thickness ET (mm):
±0.5	Thickness Tolerance (mm):

Optical Properties

N-BK7	Substrate: ☐
±2	Focal Length Tolerance (%):
80-50	Surface Quality:
12.00	Effective Focal Length EFL (mm):
24.00	Radius of Curvature (mm):
f/1	Aperture (f/#):
Protected Aluminum (400-2000nm)	Coating:
R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm	Coating Specification:
Metal	Coating Type:
24.00	Radius R ₁ (mm):
400 - 2000	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Ideal for Focusing Light
 - Aluminum and Gold Coating Options
 - Available in Sizes Ranging from 9 - 50mm
- Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

TECHNICAL INFORMATION



