

TECHSPEC®

12mm Dia. x 12mm FL Uncoated, Double-Convex Lens



Stock **#32-014** 3-4 DAYS

[Other Coating Options](#)

-

1

+

£26.35

ADD TO CART

Qty 1-9
£26.35
Qty 10+
£23.80
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Back Focal Length BFL (mm):

10.79
Effective Focal Length EFL (mm): 12.00
Coating: Uncoated
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.85
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.41
Radius R ₁ =R ₂ (mm): 15.34
Clear Aperture CA (mm): 11.00
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 380 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant