

12mm Dia. x 60mm FL, Commercial Grade, Plano-Convex Lens



Stock **#23-077** CLEARANCE **10 In Stock**

☐ [Other Coating Options](#)

-

1

+

£16^{.40}

ADD TO CART

Volume Pricing	
Qty 1+	£16.40 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

	Type:
Plano-Convex Lens	

Physical & Mechanical Properties

12.00 +0.00/-0.10	Diameter (mm):
6.00	Centering (arcmin):
	Edge Thickness ET (mm):


1.41	
	Clear Aperture CA (mm):
≥10.2	
Optical Properties	
	Effective Focal Length EFL (mm):
60.00	
	Back Focal Length BFL (mm):
58.69	
Coating:	
MgF ₂ (400-700nm)	
Coating Specification:	
R _{avg} ≤1.75% @400 - 700nm	
Substrate: ☐	
N-BK7	
	Focal Length Tolerance (%):
±1	
Radius R ₁ (mm):	
31.01	
f/#:	
5.00	
Numerical Aperture NA:	
0.10	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- Feature Standard Designs and Specifications
- Also Available [Uncoated](#)
- For Mbre Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. MgF₂ anti-reflection coating offers improved transmission in the visible spectrum. Commercial Grade MgF₂ Coated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information



Coating Curves