

TECHSPEC®

12mm f/11, 150-500mm Primary WD, HRr Series Fixed Focal Length Lens



Stock #36-862 **CLEARANCE** 6 In Stock

1

£395^{.96}

ADD TO CART

12mm, 150-500mm Primary WD, HRr Series Fixed Focal Length Lens



Volume Pricing	
Qty	£395.96 each
1+	
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	Zemax
eDrawing:eprt	
EO Spec Sheet	

General

Product Family: HRr Series	Type: Fixed Focal Length Lens
-----------------------------------	--------------------------------------

Physical & Mechanical Properties

Iris Option: Fixed	Length (mm): 39.20
Maximum Diameter (mm): 33	Outer Diameter (mm): 33
Weight (g): 77	Maximum Rear Protrusion (mm): 1.63

Optical Properties

Horizontal Field of View @ Max Sensor Format: 87.7mm - 41.1°	Field of View at Max Sensor Format: Horizontal: 87.7mm - 41.1° Vertical: 65.1mm - 31.2° Diagonal: 111mm - 50.7°
Horizontal Field of View, 2/3" Sensor: 87.7mm - 41.1°	Horizontal Field of View, 1/1.8" Sensor: 71.2mm - 33.9°
Horizontal Field of View, 1/2" Sensor: 63.1mm - 30.2°	Horizontal Field of View, 1/2.5" Sensor: 57.0mm - 27.4°
Horizontal Field of View, 1/3" Sensor: 47.0mm - 22.8°	Horizontal Field of View, 1/4" Sensor: 35.2mm - 17.1°
Maximum Image Circle (mm): 11.00	Numerical Aperture NA, Object Side: 0.0046

Number of Elements (Groups):	10 (6)	Focal Length FL (mm):	12.00
Working Distance (mm):	100 - ∞	Aperture (f/#):	f/11
Coating:	425 - 675nm BBAR	Coating Specification:	425 - 675nm BBAR
Entrance Pupil Position (mm):	17.46	Object Space Principal Plane (mm):	26.28
Image Space Principal Plane (mm):	2.98	Maximum Distortion (%):	-3.15
Exit Pupil Position (mm):	-30.39	Optimized Working Distance (mm):	150 - 500
Lens Wavelength Range:	VIS		

Sensor

Maximum Sensor Format:	2/3"	Pixel Size (µm):	1.85
-------------------------------	------	-------------------------	------

Threading & Mounting

Filter Thread:	M30.5 x 0.50 (Female)	Mount:	C-Mount
-----------------------	--------------------------	---------------	---------

Environmental & Durability Factors

Storage Temperature (°C):	-20 to +60	Type of Ruggedization:	Stabilized (Robust Mechanics for Shock and Vibration)
----------------------------------	-------------------	-------------------------------	--

Regulatory Compliance

RoHS 2015:	Compliant	Reach 209:	Compliant
Certificate of Conformance:	View		

Product Details

- 2/3", C-Mount Lens
- Up to 10 MegaPixels, 1.85µm Pixel Size Sensors
- Ruggedized (HRr) Designs (50g Shock) of our HR Series Lens with Individual Optics Glued in Place
- 8.5mm to 12mm Focal Length
- **Instrumentation (HRi) Versions** Also Available

TECHSPEC® HRr Series Fixed Focal Length Lenses are designed with a high level of machine vision performance in mind and provide stabilized ruggedization with all individual lens elements glued in place to reduce pixel shift. They are available in multiple options for each focal length to accommodate a variety of optimized working distance ranges. Additionally, the stainless steel locking C-Mount clamp and simplified focus provide added robustness. TECHSPEC HRr Series Fixed Focal Length Lenses are exemplary for calibrated imaging systems such as measurement and gauging, 3D stereo vision, robotics and sensing, autonomous vehicles, and object tracking. Call for OEM Quantity Pricing.

Edmund Optics has created a family of high performance optical designs (the HR Series family) and developed three customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the HR Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **HR Series:** Features locking cam focus and iris adjustment. This is the most adjustable version of these optical designs and is the typical high quality machine vision lens.
- **HRi Series:** Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.
- HRr Series: All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.

Technical Information

#36-862, 12mm f/11, 150-500mm Primary WD, HRr Series Fixed Focal Length Lens, Distortion Plot

#36-862, 12mm f/11, 150-500mm Primary WD, HRr Series Fixed Focal Length Lens, Relative Illumination Plot

#36-862, 12mm f/11, 150-500mm Primary WD, HRr Series Fixed Focal Length Lens, Working Distance versus Field of View Plot

#36-862, 12mm f/11, 150-500mm Primary WD, HRr Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 250mm Working Distance, f11

#36-862, 12mm f/11, 150-500mm Primary WD, HRr Series Fixed Focal Length Lens, Depth of Field Plot, 250mm Working Distance, f11

#36-862, 12mm f/11, 150-500mm Primary WD, HRr Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 450mm Working Distance, f11

#36-862, 12mm f/11, 150-500mm Primary WD, HRr Series Fixed Focal Length Lens, Depth of Field Plot, 450mm Working Distance, f11

Related Products



#89-815 - Light Red M30.5 x 0.50 High Performance Machine Vision Filter
£160.80

#89-785 - Green M30.5 x 0.50 High Performance Machine Vision Filter
£160.80

#89-765 - Blue M30.5 x 0.50 High Performance Machine Vision Filter
£160.80

#89-795 - VIS (UV/IR Cut) M30.5 x 0.50 High Performance Machine Vision Filter
£160.80










































Frequently Purchased Together





























































































#65-801 - M30.5 x 0.5 Mount for 25mm Diameter Filters
£47.20








































Compatible Cameras














































	Title	Type	Compare	Stock Number	Price	Buy
	LUCID Vision Labs Phoenix™ PHX032S-CC, Sony IMX265, 3.2 MP, Color Camera (Recertified 05-P)	Color Camera		#11-465-RCD-05P RECERTIFIED	£300.16 Request Quote	1 In Stock <input type="text" value="1"/>
	Basler ace acA1280-60gm Monochrome GigE Camera	Monochrome Camera		#89-974	£311.00 Request Quote	2 In Stock <input type="text" value="1"/>
	Basler ace acA1280-60gc Color	Color Camera		#89-975	£335.00 Request	1 In Stock <input type="text" value="1"/>














































	Title	Type	Compare	Stock Number	Price	Buy
 	GigE Camera				Quote	
 	LUCID Vision Labs Phoenix™ PHX032S-CC, Sony IMX265, 3.2 MP, Color Camera	Color Camera		#11-465	£375.20 Request Quote	3 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX032S-CC-IX, Sony IMX265, 3.2 MP, Color Camera	Color Camera		#13-678	£375.20 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX032S-MC, Sony IMX265, 3.2 MP, Monochrome Camera	Monochrome Camera		#11-464	£375.20 Request Quote	2 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX032S-MC-IX, Sony IMX265, 3.2 MP, Monochrome Camera	Monochrome Camera		#13-677	£375.20 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI054S-CC, Sony IMX490, 5.4MP, Color Camera	Color Camera		#17-101	£379.20 Request Quote	5 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX050S-CC, Sony IMX264, 5.0 MP, Color Camera	Color Camera		#11-467	£400.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX050S-CC-IX, Sony IMX264, 5.0 MP, Color Camera	Color Camera		#13-686	£400.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX050S-MC, Sony IMX264, 5.0 MP, Monochrome Camera	Monochrome Camera		#11-466	£400.00 Request Quote	5 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX050S-MC-IX, Sony IMX264, 5.0 MP, Monochrome Camera	Monochrome Camera		#13-685	£400.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI032S-CC, Sony IMX265, 3.2MP, Color Camera	Color Camera		#13-716	£416.00 Request Quote	4 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI032S-MC, Sony IMX265, 3.2MP, Monochrome Camera	Monochrome Camera		#13-715	£416.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#14-875	£416.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, USB 3.0	Color Camera		#14-876	£424.00 Request Quote	CONTACT US <input type="text" value="1"/> 











































	Title	Type	Compare	Stock Number	Price	Buy
	Color Camera (Partial Housing)					
 	Basler ace acA1300-60gm Monochrome GigE Camera	Monochrome Camera		#88-327	£424.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C- Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#14-871	£424.00 Request Quote	20+ In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C- Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#14-873	£424.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C- Mount, USB 3.0 Color Camera	Color Camera		#14-872	£432.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C- Mount, Right Angle USB 3.1 Color Camera	Color Camera		#14-874	£432.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI051S- CC, Sony IMX547, 5MP, Color Camera	Color Camera		#18-483	£436.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI051S- MC, Sony IMX547, 5MP, Monochrome Camera	Monochrome Camera		#18-484	£436.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI050S- CC, Sony IMX264, 5.0MP, Color Camera	Color Camera		#12-758	£440.00 Request Quote	4 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI028S- CC, Sony IMX429, 2.8MP, Color Camera	Color Camera		#17-098	£440.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI050S- MC, Sony IMX264, 5.0MP, Monochrome Camera	Monochrome Camera		#12-757	£440.00 Request Quote	4 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI028S- MC, Sony IMX429, 2.8MP, Monochrome Camera	Monochrome Camera		#17-097	£440.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Basler ace acA1300-60gc Color GigE Camera	Color Camera		#88-328	£448.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-PGE-31S4C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#11-528	£452.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-U3-31S4C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#12-750	£452.00 Request Quote	CONTACT US <input type="text" value="1"/> 














































	Title	Type	Compare	Stock Number	Price	Buy
 	BFS-PGE-31S4M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#11-527	£452.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-31S4M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#12-749	£452.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2040-35gm Monochrome GigE Camera	Monochrome Camera		#35-915	£456.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium G1-319m, 1/1.8" 3.2MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-547	£464.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFLY-PGE-31S4M/C- C 1/1.8" Blackfly® PoE GigE Color Camera	Color Camera		#34-510	£468.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFLY-PGE-31S4M/C- C 1/1.8" Blackfly® PoE GigE Monochrome Camera	Monochrome Camera		#34-511	£468.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium G1-319c, 1/1.8" 3.2MP C-Mount, GigE PoE Color Camera	Color Camera		#23-548	£472.00 Request Quote	5 In Stock <input type="text" value="1"/> 
 	Basler ace acA2040-35gc Color GigE Camera	Color Camera		#35-916	£480.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	M2020, 1/1.8" Monochrome, DALSA Genie Nano GigE PoE Camera	Monochrome Camera		#34-960	£484.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Mako G-131B 1/1.8" Monochrome CMOS Camera	Monochrome Camera		#33-514	£488.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	C2020-IR, 1/1.8" Color, DALSA Genie Nano GigE PoE Camera	Color Camera		#34-961	£496.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Mako G-131C 1/1.8" Color CMOS Camera	Color Camera		#33-515	£504.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Mako G-319 1/1.8" Color CMOS Camera (Recertified 05-P)	Color Camera		#36-175-RCD-05P RECERTIFIED	£508.80 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-PGE-50S4C-C, PoE GigE Blackfly® S, Color Camera (Recertified 05-P)	Color Camera		#22-080-RCD-05P RECERTIFIED	£520.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-PGE-19S4C-C, PoE GigE Blackfly® S, Color Camera	Color Camera		#22-077	£524.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-19S4C-C, USB 3.1 Blackfly® S, Color Camera	Color Camera		#22-089	£524.00 Request Quote	1 In Stock <input type="text" value="1"/> 














































	Title	Type	Compare	Stock Number	Price	Buy
 	BFS-PGE-19S4M-C, PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#22-078	£524.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-19S4M-C, USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#22-090	£524.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	IDS U3-3270CP-C-HQ REV.2.2, USB 3.0, 1/1.8" Color Camera	Color Camera		#16-528	£536.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Mako G-192B 1/1.8" Monochrome CMOS Camera	Monochrome Camera		#33-516	£536.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-566	£536.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-565	£536.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX050S1-QC, Sony IMX264MYR, 5.0 MP, Polarized Color Camera	Polarized Color Camera		#19-624	£536.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX050S1-PC, Sony IMX264MZR, 5.0 MP, Polarized Monochrome Camera	Polarized Monochrome Camera		#19-623	£536.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)	Color Camera		#19-578	£544.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#19-577	£544.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA1920-48gm Monochrome GigE Camera	Monochrome Camera		#35-913	£544.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA1920-150um Monochrome USB 3.0 Camera	Monochrome Camera		#36-739	£544.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#19-560	£544.00 Request Quote	3 In Stock <input type="text" value="1"/> 


















































	Title	Type	Compare	Stock Number	Price	Buy
 	Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#19-559	£544.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Mako G-192C 1/1.8" Color CMOS Camera	Color Camera		#33-517	£552.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Color Camera	Color Camera		#19-572	£552.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, USB 3.0 Color Camera	Color Camera		#19-571	£552.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA1920-48gc Color GigE Camera	Color Camera		#35-914	£560.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA1920-150uc Color USB 3.0 Camera	Color Camera		#36-740	£560.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Basler ace acA2040-55um Monochrome USB 3.0 Camera	Monochrome Camera		#35-921	£560.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-PGE-27S5C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#13-921	£572.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-27S5C-C, USB 3.1 Blackfly® S, Color Camera	Color Camera		#22-093	£572.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	M1930, 2/3" Monochrome, DALSA Genie Nano GigE PoE Camera	Monochrome Camera		#34-958	£572.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-PGE-27S5M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#13-920	£572.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-U3-27S5M-C, USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#22-094	£572.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA2040-55uc Color USB 3.0 Camera	Color Camera		#35-922	£576.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI081S-CC, Sony IMX546, 8.1MP, Color Camera	Color Camera		#18-481	£584.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI081S-MC, Sony IMX546, 8.1MP, Monochrome Camera	Monochrome Camera		#18-482	£584.00 Request Quote	1 In Stock <input type="text" value="1"/> 






























	Title	Type	Compare	Stock Number	Price	Buy
 	LUCID Vision Labs Triton™ TRI050S1-QC, Sony IMX264MYR, 5.0 MP, Polarized Color Camera	Polarized Color Camera		#19-626	£584.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI050S1-PC, Sony IMX264MZR, 5.0 MP, Polarized Monochrome Camera	Polarized Monochrome Camera		#19-625	£584.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	BFS-PGE-50S4C-C, PoE GigE Blackfly® S, Color Camera	Color Camera		#22-080	£592.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-50S4C-C, USB 3.1 Blackfly® S, Color Camera	Color Camera		#22-765	£592.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-PGE-50S4M-C, PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#22-081	£592.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-U3-50S4M-C, USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#22-766	£592.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	C1930-IR, 2/3" Color, DALSA Genie Nano GigE PoE Camera	Color Camera		#34-959	£608.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-291m, 2/3" 2.9MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#23-166	£608.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-291m, 2/3" 2.9MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#23-190	£608.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-291c, 2/3" 2.9MP C-Mount, USB 3.0 Color Camera	Color Camera		#23-167	£616.00 Request Quote	5 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-291c, 2/3" 2.9MP C-Mount, Right Angle USB 3.1 Color Camera	Color Camera		#23-191	£616.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	IDS U3-3160CP-C-HQ, USB 3.0, 2/3" Color Camera	Color Camera		#24-081	£624.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA1600-60gm Monochrome GigE Camera	Monochrome Camera		#88-330	£624.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	IDS U3-3160CP-M-GL, USB 3.0, 2/3" Monochrome Camera	Monochrome Camera		#24-082	£624.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-507m, 2/3" 5.1MP C-Mount, USB 3.0 Monochrome	Monochrome Camera		#14-881	£640.00 Request Quote	CONTACT US <input type="text" value="1"/> 

















































	Title	Type	Compare	Stock Number	Price	Buy
	Camera (Partial Housing)					
 	Allied Vision Alvium 1800 U-507m, 2/3" 5.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera (Partial Housing)	Monochrome Camera		#14-883	£640.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Flea®3 FL3-U3-13E4C-C 1/1.8" Color USB 3.0 Camera	Color Camera		#87-432	£648.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-507c, 2/3" 5.1MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#14-882	£648.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-507c, 2/3" 5.1MP C-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)	Color Camera		#14-884	£648.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Flea®3 FL3-U3-13E4M-C 1/1.8" Monochrome USB 3.0 Camera	Monochrome Camera		#87-431	£648.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-507m, 2/3" 5.1MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#14-877	£648.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-507m, 2/3" 5.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#14-879	£648.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA1600-60gc Color GigE Camera	Color Camera		#88-331	£656.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-507c, 2/3" 5.1MP C-Mount, USB 3.0 Color Camera	Color Camera		#14-878	£656.00 Request Quote	11 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-507c, 2/3" 5.1MP C-Mount, Right Angle USB 3.1 Color Camera	Color Camera		#14-880	£656.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Mako G-319 1/1.8" Monochrome CMOS Camera	Monochrome Camera		#36-174	£672.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Mako G-319 1/1.8" Color CMOS Camera	Color Camera		#36-175	£688.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	M1930, 2/3" NIR, Teledyne DALSA Genie Nano GigE PoE Camera	NIR Camera		#14-676	£692.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Manta G-0319 1/1.8" Color Camera	Color Camera		#34-717 CLEARANCE	£695.16 Request Quote	CONTACT US <input type="text" value="1"/> 










































	Title	Type	Compare	Stock Number	Price	Buy
 	BFS-PGE-50S5C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#36-561	£704.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-50S5C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#12-752	£704.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA2440-35um Monochrome USB 3.0 Camera	Monochrome Camera		#35-925	£704.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA2440-20gm Monochrome GigE Camera	Monochrome Camera		#35-917	£704.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-PGE-50S5M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#36-560	£704.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-50S5M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#12-751	£704.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium G1-507m, 2/3" 5.1MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-555	£704.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA1300-60gm-NIR GigE Camera	NIR Camera		#88-329	£704.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium G1-507c, 2/3" 5.1MP C-Mount, GigE PoE Color Camera	Color Camera		#23-556	£712.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-811m, 2/3" 8.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-586	£712.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-811m, 2/3" 8.1MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-585	£712.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA2440-35uc Color USB 3.0 Camera	Color Camera		#35-926	£720.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA2440-20gc Color GigE Camera	Color Camera		#35-918	£720.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-811c, 2/3" 8.1MP C-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)	Color Camera		#19-590	£720.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-811c, 2/3" 8.1MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#19-589	£720.00 Request Quote	CONTACT US <input type="text" value="1"/> 





























	Title	Type	Compare	Stock Number	Price	Buy
 	Allied Vision Alvium 1800 U-811m, 2/3" 8.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#19-584	£720.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-811m, 2/3" 8.1MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#19-583	£720.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium G1-811m, 2/3" 8.1MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-561	£720.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-U3-32S4C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#36-454	£724.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-32S4M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#36-453	£724.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-811c, 2/3" 8.1MP C-Mount, Right Angle USB 3.1 Color Camera	Color Camera		#19-588	£728.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-811c, 2/3" 8.1MP C-Mount, USB 3.0 Color Camera	Color Camera		#19-587	£728.00 Request Quote	8 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium G1-811c, 2/3" 8.1MP C-Mount, GigE PoE Color Camera	Color Camera		#23-562	£728.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-20S4C-C, USB 3.1 Blackfly® S, Color Camera	Color Camera		#22-091	£728.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-20S4M-C, USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#22-092	£728.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	PL-D722-AF-ED Pixelink USB 3.0 Autofocus Monochrome Camera	Monochrome Camera		#34-777 CLEARANCE	£728.76 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFLY-PGE-50S5C-C 2/3" Blackfly® PoE GigE Color Camera	Color Camera		#34-512	£736.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFLY-PGE-50S5M-C 2/3" Blackfly® PoE GigE Monochrome Camera	Monochrome Camera		#34-513	£736.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Atlas™ ATLO28S-MC, Sony IMX421, 2.8MP, Monochrome Camera (Recertified 05-P)	Monochrome Camera		#17-108-RCD-05P RECERTIFIED	£765.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-28S5C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#13-925	£784.00 Request Quote	CONTACT US <input type="text" value="1"/> 




























	Title	Type	Compare	Stock Number	Price	Buy
 	Basler ace acA2040-120um Monochrome USB 3.0 Camera	Monochrome Camera		#35-923	£784.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	BFS-U3-28S5M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#13-924	£784.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA2040-120uc Color USB 3.0 Camera	Color Camera		#35-924	£800.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	IDS U3-3280CP-C-HQ, USB 3.0, 2/3" Color Camera	Color Camera		#16-532	£808.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-0319 1/1.8" Monochrome Camera	Monochrome Camera		#34-716	£808.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	IDS U3-3280CP-M-GL, USB 3.0, 2/3" Monochrome Camera	Monochrome Camera		#16-533	£808.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	IDS U3-3070CP-C-HQ, USB 3.0, 1/1.8" Color Camera	Color Camera		#16-512	£816.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	IDS U3-3070CP-M-GL, USB 3.0, 1/1.8" Monochrome Camera	Monochrome Camera		#16-513	£816.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	M2420, 2/3" Monochrome, DALSA Genie Nano GigE PoE Camera	Monochrome Camera		#34-962	£820.00 Request Quote	9 In Stock <input type="text" value="1"/> 
 	Allied Vision Mako G-507 2/3" Monochrome CMOS Camera	Monochrome Camera		#36-176	£832.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	C2420-IR, 2/3" Color, DALSA Genie Nano GigE PoE Camera	Color Camera		#34-963	£836.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Mako G-507 2/3" Color CMOS Camera	Color Camera		#36-177	£848.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Manta G-319C Color CMOS PoE Camera	Color Camera		#37-511	£856.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-319B Monochrome CMOS PoE Camera	Monochrome Camera		#37-510	£856.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	GS3-U3-32S4C-C 1/1.8" FLIR Grasshopper®3 High Performance USB 3.0 Color Camera	Color Camera		#33-535	£924.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	GS3-U3-32S4M-C 1/1.8" FLIR Grasshopper®3 High Performance USB 3.0 Monochrome Camera	Monochrome Camera		#33-534	£924.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	Pixelink PL-D753CU-BL, 2/3"	Color Camera		#14-162	£952.00 Request	CONTACT US <input type="text" value="1"/> 
































		Title	Type	Compare	Stock Number	Price	Buy
MORE+		2.8MP, Board Level USB 3.0 Color Camera				Quote	
MORE+		Pixelink PL-D753MU-BL, 2/3" 2.8MP, Board Level USB 3.0 Monochrome Camera	Monochrome Camera		#14-161	£952.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+		Allied Vision Alvium 1800 U-508m, 2/3" 5.07MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#17-087	£952.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+		Allied Vision Alvium 1800 U-508c, 2/3" 5.07MP C-Mount, USB 3.0 Color Camera	Color Camera		#17-088	£960.00 Request Quote	4 In Stock <input type="text" value="1"/> 
MORE+		Allied Vision Manta G-319C Color CMOS PoE Camera (Recertified 05-P)	Color Camera		#37-511-RCD-05P RECERTIFIED	£986.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+		Allied Vision Manta G-507 2/3" Color Camera	Color Camera		#34-719	£1,000.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+		Allied Vision Manta G-507 2/3" Monochrome Camera	Monochrome Camera		#34-718	£1,000.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+		Allied Vision Manta G-507 2/3" Color Camera (Recertified 05-P)	Color Camera		#34-719-RCD-05P RECERTIFIED	£1,020.00 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+		LUCID Vision Labs Atlas™ ATL028S-CC, Sony IMX421, 2.8MP, Color Camera	Color Camera		#17-109	£1,032.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+		LUCID Vision Labs Atlas™ ATL028S-MC, Sony IMX421, 2.8MP, Monochrome Camera	Monochrome Camera		#17-108	£1,032.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+		Allied Vision Alvium G5-811m, 2/3" 8.1MP C-Mount, 5GigE PoE Monochrome Camera	Monochrome Camera		#23-629	£1,032.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+		Allied Vision Alvium G5-811c, 2/3" 8.1MP C-Mount, 5GigE PoE Color Camera	Color Camera		#23-630	£1,040.00 Request Quote	8 In Stock <input type="text" value="1"/> 
MORE+		BFS-U3-51S5C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#36-456	£1,044.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+		BFS-U3-51S5M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#36-455	£1,044.00 Request Quote	4 In Stock <input type="text" value="1"/> 
MORE+		Allied Vision Manta G-507C Color CMOS PoE Camera	Color Camera		#37-513	£1,048.00 Request Quote	1 In Stock <input type="text" value="1"/> 



	Title	Type	Compare	Stock Number	Price	Buy
	 Allied Vision Manta G-507B Monochrome CMOS PoE Camera	Monochrome Camera		#37-512	£1,048.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 M2450, 2/3" Monochrome, Teledyne DALSA Genie Nano 5GigE PoE Camera (Recertified 05-P)	Monochrome Camera		#16-026-RCD-05P RECERTIFIED	£1,112.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Mako G-223B 2/3" Monochrome CMOS Camera	Monochrome Camera		#88-469	£1,120.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Pixelink M-Series M2M-CYL Microscopy Monochrome Camera	Monochrome Microscopy Camera		#17-818	£1,120.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 PL-D722-AF-ED Pixelink USB 3.0 Autofocus Color Camera	Color Camera		#34-778	£1,124.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Mako G-223C 2/3" Color CMOS Camera	Color Camera		#88-470	£1,136.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace acA2000-165um Monochrome USB 3.0 Camera	Monochrome Camera		#89-987	£1,168.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Basler ace acA2440-75um Monochrome USB 3.0 Camera	Monochrome Camera		#35-927	£1,184.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace acA2000-165uc Color USB 3.0 Camera	Color Camera		#89-988	£1,192.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Basler ace acA2440-75uc Color USB 3.0 Camera	Color Camera		#35-928	£1,200.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Manta G-223B Monochrome CMOS PoE Camera	Monochrome Camera		#13-935	£1,200.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 LUCID Vision Labs Atlas™ ATL050S-CC, Sony IMX250, 5.0MP, Color Camera	Color Camera		#13-738	£1,232.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace acA2000-50gm Monochrome GigE Camera	Monochrome Camera		#87-101	£1,232.00 Request Quote	3 In Stock <input type="text" value="1"/> 
	 LUCID Vision Labs Atlas™ ATL050S-MC, Sony IMX250, 5.0MP, Monochrome Camera	Monochrome Camera		#13-737	£1,232.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Alvium G5-508m, 2/3" 5.1MP C-Mount, 5GigE PoE Monochrome Camera	Monochrome Camera		#23-623	£1,248.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Basler ace acA2000-50gc Color GigE Camera	Color Camera		#87-102	£1,256.00 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	Allied Vision Alvium G5-508c, 2/3" 5.1MP C-Mount, 5GigE PoE Color Camera	Color Camera		#23-624	£1,256.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	M2050, 1/1.8" Monochrome, Teledyne DALSA Genie Nano 5GigE PoE Camera	Monochrome Camera		#16-024	£1,280.00 Request Quote	4 In Stock <input type="text" value="1"/> 
 	IDS U3-3080CP-C-HQ, USB 3.0, 2/3" Color Camera	Color Camera		#16-516	£1,288.00 Request Quote	5 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D795CU-T, 2/3" 5.0MP, C-Mount USB 3.0 Color Camera	Color Camera		#38-006	£1,292.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D753CU-T, 2/3" 2.8MP, C-Mount USB 3.0 Color Camera	Color Camera		#14-160	£1,292.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	C2050-IR, 1/1.8" Color, Teledyne DALSA Genie Nano 5GigE PoE Camera	Color Camera		#16-025	£1,292.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D795MU-T, 2/3" 5.0MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#38-005	£1,292.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D753MU-T, 2/3" 2.8MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#14-159	£1,292.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	PL-D753CU-AF-ED Pixelink USB 3.0 Autofocus Color Camera	Color Camera		#14-181	£1,296.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	PL-D753MU-AF-ED Pixelink USB 3.0 Autofocus Monochrome Camera	Monochrome Camera		#14-180	£1,296.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	PL-D732-AF-ED Pixelink USB 3.0 Autofocus Color Camera	Color Camera		#34-782	£1,320.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	PL-D732-AF-ED Pixelink USB 3.0 Autofocus Monochrome Camera	Monochrome Camera		#34-781	£1,320.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D722CU-T, 2/3" 2.3MP, C-Mount USB 3.0 Color Camera	Color Camera		#89-383	£1,380.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	GS3-U3-51S5C-C 2/3" FLIR Grasshopper®3 High Performance USB 3.0 Color Camera	Color Camera		#33-539	£1,392.00 Request Quote	3 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	GS3-U3-51S5M-C 2/3" FLIR Grasshopper®3 High Performance USB 3.0 Monochrome Camera	Monochrome Camera		#33-538	£1,392.00 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	Oryx® ORX-10GS- 32S4C-C Color 10GigE	Color Camera		#19-797	£1,420.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Oryx® ORX-10GS- 32S4M-C Mono 10GigE	Monochrome Camera		#19-796	£1,420.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	M2450, 2/3" Monochrome, Teledyne DALSA Genie Nano 5GigE PoE Camera	Monochrome Camera		#16-026	£1,460.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Pixelink PL- D732CU-T, 2/3" 2.2MP, C-Mount USB 3.0 Color Camera	Color Camera		#33-339	£1,468.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Pixelink PL- D755CU-BL, 2/3" 5.0MP, Board Level USB 3.0 Color Camera	Color Camera		#11-439	£1,468.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Pixelink PL- D732MU-T, 2/3" 2.2MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#33-338	£1,468.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Pixelink PL- D755MU-BL, 2/3" 5.0MP, Board Level USB 3.0 Monochrome Camera	Monochrome Camera		#11-438	£1,468.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	C2450-IR, 2/3" Color, Teledyne DALSA Genie Nano 5GigE PoE Camera	Color Camera		#16-027	£1,476.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Atlas10 ATX051S- CC, Sony IMX537, 5.0MP, Color Camera	Color Camera		#18-477	£1,524.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Atlas10 ATX051S- MC, Sony IMX537, 5.0MP, Monochrome Camera	Monochrome Camera		#18-478	£1,524.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Pixelink PL- D755CU-T, 2/3" 5.0MP, C-Mount USB 3.0 Color Camera	Color Camera		#11-437	£1,552.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Pixelink PL- D755MU-T, 2/3" 5.0MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#11-436	£1,552.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Prosilica GT2000 2/3" Color CMOS Camera	Color Camera		#87-080	£1,568.00 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	Allied Vision Prosilica GT2000 2/3" Monochrome CMOS Camera	Monochrome Camera		#87-079	£1,568.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX050S-QC, Sony IMX250MYR, 5.0 MP, Polarized Color Camera	Polarized Color Camera		#13-694	£1,608.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX050S-QC-IX, Sony IMX250MYR, 5.0 MP, Polarized Color Camera	Polarized Color Camera		#13-698	£1,608.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX050S-PC, Sony IMX250MZR, 5.0 MP, Polarized Monochrome Camera	Polarized Monochrome Camera		#13-693	£1,608.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX050S-PC-IX, Sony IMX250MZR, 5.0 MP, Polarized Monochrome Camera	Polarized Monochrome Camera		#13-697	£1,608.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Pixelink M-Series M2C-CYL Microscopy Color Camera	Color Microscopy Camera		#17-817	£1,640.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Prosilica GT2000 2/3" NIR CMOS Camera	NIR Camera		#88-475	£1,664.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Triton™ TRI050S-QC, Sony IMX250MYR, 5.0MP, Polarized Color Camera	Polarized Color Camera		#13-724	£1,696.00 Request Quote	4 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Triton™ TRI050S-PC, Sony IMX250MZR, 5.0MP, Polarized Monochrome Camera	Polarized Monochrome Camera		#13-723	£1,696.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Pixelink M-Series M5DC-CYL Microscopy Color Camera	Color Microscopy Camera		#17-823	£1,728.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Pixelink M-Series M5DM-CYL Microscopy Monochrome Camera	Monochrome Microscopy Camera		#17-824	£1,728.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Atlas10 ATX081S-CC, Sony IMX536, 8.1MP, Color Camera	Color Camera		#18-475	£1,732.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Atlas10 ATX081S-MC, Sony IMX536, 8.1MP, Monochrome Camera	Monochrome Camera		#18-476	£1,732.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	Oryx® ORX-10GS-51S5C-C Color	Color Camera		#19-795	£1,808.00 Request	3 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	10GigE				Quote	
MORE+ 	Oryx® ORX-10GS-51S5M-C Mono 10GigE	Monochrome Camera		#19-794	£1,808.00 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Prosilica GT2460C 2/3" Color CCD Camera	Color Camera		#13-944	£1,888.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Prosilica GT2460B 2/3" Monochrome CCD Camera	Monochrome Camera		#13-943	£1,888.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-U3-51S5PC-C USB 3.1 Blackfly® S, Polarized Color Camera	Polarized Color Camera		#13-928	£1,920.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-PGE-51S5PC-C PoE GigE Blackfly® S, Polarized Color Camera	Polarized Color Camera		#13-929	£1,920.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	BFS-U3-51S5P-C USB 3.1 Blackfly® S, Polarization Monochrome Camera	Polarized Monochrome Camera		#12-793	£1,920.00 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-PGE-51S5P-C PoE GigE Blackfly® S, Polarization Monochrome Camera	Polarized Monochrome Camera		#12-794	£1,920.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	PL-D755-AF-ED Pixelink USB 3.0 Autofocus Color Camera	Color Camera		#34-784	£1,984.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	PL-D755-AF-ED Pixelink USB 3.0 Autofocus Monochrome Camera	Monochrome Camera		#34-783	£1,984.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Lumenera INFINITY 3-3UR Microscopy Monochrome Camera	Monochrome Microscopy Camera		#33-275 CLEARANCE	£2,759.16 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Lumenera INFINITY5 5-3 Microscopy Color Camera	Color Microscopy Camera		#16-678	£2,980.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Lumenera INFINITY5 5-3 Microscopy Monochrome Camera	Monochrome Microscopy Camera		#16-677	£2,980.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Lumenera INFINITY5 5-5 Microscopy Color Camera	Color Microscopy Camera		#16-680	£3,420.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Lumenera INFINITY5 5-5 Microscopy Monochrome Camera	Monochrome Microscopy Camera		#16-679	£3,420.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Pixelink PL-D755MU-BL-POL, 2/3" 5.0MP, Board Level USB 3.0 Polarized Monochrome Camera	Polarized Monochrome Camera		#14-158	£3,456.00 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	Pixelink PL-D755MU-T-POL, 2/3" 5.0MP, C-Mount USB 3.0 Polarized Monochrome Camera	Polarized Monochrome Camera		#14-157	£3,544.00 Request Quote	CONTACT US <input type="text" value="1"/> 

Resources

Media Type

- Application Note
- Video
- Trending in Optics
- Published Article
- FAQ
- Glossary
- Technical Tool

APPLICATION NOTE

Anti-Reflection (AR) Coatings

APPLICATION NOTE

An Introduction to Optical Coatings

VIDEO

Wavelength and f#

APPLICATION NOTE

Understanding Focal Length and Field of View

APPLICATION NOTE

Introduction to Modulation Transfer Function

VIDEO

LIGHT TALK - EPISODE 5: Ruggedized Imaging

[View More](#)