

13mm Travel, 0.01mm Grad. Mic. Drive F-Face



Drive Mechanisms

Stock **#33-726** **1 In Stock**

-

1

+

£73¹⁰

ADD TO CART

Volume Pricing	
Qty 1+	£73.10 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General	
	Type:
Metric	
	Manufacturer:
Mitutoyo	

Physical & Mechanical Properties	
13	Travel (mm):
0.01	Graduation (mm):
9.5	Stem Diameter (mm):
Plain/Flat	Stem/Spindle:
9.5	Stem Length (mm):
5	Spindle Diameter (mm):
15.5	Min. Spindle Length (mm):
13	Max. Diameter (mm):
62	Overall Length (mm):
Hardware & Interface Connectivity	
Metric Micrometer	Type of Drive:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

PRODUCT DETAILS

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.
- Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

TECHNICAL INFORMATION

