

TECHSPEC® 1310nm, 25.4mm Dia. x 6.35mm Thickness, Ultrafast Laser Mirror



Stock **#28-996** [CONTACT US](#)

-

1

+

£180^{.80}

ADD TO CART

Volume Pricing	
Qty 1-5	£180.80 each
Qty 6-25	£163.20 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror

Type:

Physical & Mechanical Properties

6.35 ±0.20

Thickness (mm):

25.40 +0.00/-0.10

Diameter (mm):

90	Clear Aperture (%):
Commercial Polish	Back Surface:
<3	Parallelism (arcmin):

Optical Properties

Fused Silica	Substrate: □
10-5	Surface Quality:
45	Angle of Incidence (°):
Ultrafast (1260 - 1360nm)	Coating:
1310	Design Wavelength DWL (nm):
1260 - 1360	Wavelength Range (nm):
λ/8	Surface Flatness (P-V):
Coating Specification: R (AVG) S & P > 99.90% @ 1310nm @ 45° AOI R (AVG) > 99.7% @ 1260 - 1360nm @ 45° AOI	

Dielectric	Coating Type:
GDD Specification: GDDs: ±20 fs ² @ 1260 - 1360nm @ 45° AOI GDDp: ±30 fs ² @ 1285 - 1335 nm @ 45° AOI	

Environmental & Durability Factors

MIL-PRF-13830B	Durability:
----------------	-------------

Regulatory Compliance

View	Certificate of Conformance:
------	-----------------------------

Product Details

- GDD as Low as ±20fs² at Design Wavelength Range
- Greater than 99.9% Reflectivity
- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers

TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors feature a multilayer dielectric coating on fused silica substrates for excellent reflectivity of greater than 99.9%, and low coefficient of thermal expansion, making them ideal for ultrafast beam transport applications. These mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors are ideal for utilizing the first and second harmonic of Ti:sapphire and Yb:doped lasers for applications such as laser machining and welding.

Note: Please [contact us](#) if your application requires a TECHSPEC Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).