


[See all 17 Products in Family](#)

15° Fan Angle, 400 - 500nm AR Coated, High Precision Powell Lens



Stock **#70-130** [CONTACT US](#)

-

1

+

£260^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	£260.00 each
Qty 11-49	£233.60 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Beam Shaping Lens

Type:

Physical & Mechanical Properties

8.90 +0.00/-0.15

Dimensions (mm):

8.90 +0.00/-2.00

Height (mm):

Input Beam Diameter, 1/e ² (mm):	
1.3	
Optical Properties	
N-BK7	Substrate:
	Coating:
BBAR (400-500nm)	
Wavelength Range (nm):	
400 - 500	
Coating Specification:	
R _{abs} <1.0% @ 400 - 500nm	
Index of Refraction (n _d):	
1.458	
Fan Angle (°):	
15.00	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- Generate Uniform, Flat-Top Profile Over Entire Line
- Fan Angles from 1° to 75° Available
- AR Coated for 400 - 500nm or 500 - 850nm

Precision Powell Lenses, also known as aspheric line generators (ALGs), spread an input beam across a uniform line with a top-hat beam profile at a specified fan angle. These Powell lenses are produced through a precision manufacturing process to ensure high contained power, uniformity, and line straightness across the entire produced line, as well as superior part-to-part consistency. They are designed for a specific input beam diameter to provide best line uniformity; larger input beams will result in higher intensity at the ends of the generated line, while smaller will create a more Gaussian distribution. Precision Powell Lenses are ideal for use in machine vision and life science applications including 3D profile measurement, PCB inspection, line-scan SD-OCT, line-scan confocal microscopy, flow cytometry, and particle analysis.