

TECHSPEC[®] 15.0mm 750 - 1100nm Coated, N-BK7 Right Angle Mirror



Broadband Dielectric Coated Right Angle Mirrors

Stock #87-399 3-4 DAYS

-

1

+

£121.55

ADD TO CART

Qty 1-5

£121.55

Qty 6+

£97.33

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Dielectric Mirror (750-1100nm)

Coating Specification:
Hypotenuse: R_{avg} >98% @ 750 - 1100nm (0 - 45°)
R_{avg} >99% @ 750 - 1100nm (0°)

Wavelength Range (nm):

750 - 1100
Length of Legs (mm): 15.00
Length of Hypotenuse (mm): 21.20
Surface Flatness (P-V): λ/8
Substrate: ☐ N-BK7
Surface Quality: 40-20
Dimensional Tolerance (mm): ±0.1
Coating Type: Dielectric
Angle Tolerance (arcmin): ±2
Clear Aperture (%): 90
Type: Right Angle Mirror
Damage Threshold, By Design: ☐ 1 J/cm2 @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View