

TECHSPEC® 15mm 1064nm, Laser Line $\lambda/20$ High Tolerance Right Angle Mirror



Stock **#37-662** [CONTACT US](#)

- 1 + **£209.95**

ADD TO CART

Qty 1-5
£209.95

Qty 6+
£167.88

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 $\lambda/20$

Substrate: [Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Length of Legs (mm): 15.00
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R _{abs} >99.8% @ 1064nm @ 45° AOI R _{avg} >99.5% @ 1046 - 1074nm @ 45° AOI
Coating: Laser Mirror (1064nm)
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Design Wavelength DWL (nm): 1064
Length of Hypotenuse (mm): 21.20
Type: Right Angle Mirror
Pyramid Tolerance (arcmin): ±1
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference: ☐ 1MW/cm² @ 1064nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View