

TECHSPEC[®] 15mm 532nm, Laser Line $\lambda/20$ High Tolerance Right Angle Mirror



Stock #37-655 3-4 DAYS

-

1

+

£209.95

ADD TO CART

Qty 1-5

£209.95

Qty 6+

£167.88

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 $\lambda/20$

Substrate:

Fused Silica

 (Corning 7980)

Surface Quality:
20-10

Length of Legs (mm): 15.00
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R _{abs} >99.8% @ 532nm @ 45° AOI R _{avg} >99.5% @ 523 - 537nm @ 45° AOI
Coating: Laser Mirror (532nm)
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Design Wavelength DWL (nm): 532
Length of Hypotenuse (mm): 21.20
Type: Right Angle Mirror
Pyramid Tolerance (arcmin): ±1
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference:  1MW/cm² @ 532nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View