

[See all 18 Products in Family](#)

**TECHSPEC® 15mm Dia., 0.25 NA, V-Coated 1550nm NIR Aspheric Lens**



Stock #22-937 **5 In Stock**

[Other Coating Options](#)

1 **£303<sup>20</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £303.20 each                  |
| Qty 6-10       | £272.80 each                  |
| Qty 11-25      | £254.40 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Aspheric Lens **Type:**

**Physical & Mechanical Properties**

15.00 +0.0/-0.025 **Diameter (mm):**

|                      |                                  |
|----------------------|----------------------------------|
| <3                   | <b>Centering (arcmin):</b>       |
| 13.5                 | <b>Clear Aperture CA (mm):</b>   |
| 3.76                 | <b>Edge Thickness ET (mm):</b>   |
| 5.00 ±0.1            | <b>Center Thickness CT (mm):</b> |
| Protective as needed | <b>Bevel:</b>                    |
| Plano                | <b>Shape of Back Surface:</b>    |

## Optical Properties

|                                      |  |
|--------------------------------------|--|
| 30.00 @ 1550nm                       | <b>Effective Focal Length EFL (mm):</b>                      |
| 0.25                                 | <b>Numerical Aperture NA:</b>                                |
| 25.65 @ 587.6nm                      | <b>Back Focal Length BFL (mm):</b>                           |
| N-SF6                                | <b>Substrate:</b> <input type="checkbox"/>                   |
| 1550                                 | <b>Aspheric Design Wavelength (nm):</b>                      |
| 1550nm V-Coat                        | <b>Coating:</b>  |
| $R_{abs} < 0.25\%$ @ 1550nm @ 0° AOI | <b>Coating Specification:</b>                                |
| 40-20                                | <b>Surface Quality:</b>                                      |
| 2                                    | <b>f#:</b>   |
| Infinite                             | <b>Conjugate Distance:</b>                                   |
| 5 J/cm <sup>2</sup> @ 1550nm, 10ns   | <b>Damage Threshold, By Design:</b> <input type="checkbox"/> |
| 0.4λ RMS and 2λ PV                   | <b>Asphere Figure Error, @ 632.8nm:</b>                      |
| 33.33                                | <b>Power (diopters):</b>                                     |

## Environmental & Durability Factors

|   |                    |
|---|--------------------|
| ADHESION AND ABRASION AS PER MIL-PRF13830B APP C, PARAC.3.8.4 AND C.3.8.5 | <b>Durability:</b> |
|---|--------------------|

## Regulatory Compliance

|                           |                                    |
|---------------------------|------------------------------------|
| <a href="#">Compliant</a> | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>      | <b>Certificate of Conformance:</b> |
| <a href="#">Compliant</a> | <b>Reach 235:</b>                  |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Designed at 1550nm
- Precision Grade Aspheric Surface
- Uncoated and <0.25% Reflectance V-Coat Options

TECHSPEC® 1550nm Precision Near-Infrared (NIR) Aspheric Lenses are designed at 1550nm to eliminate spherical aberration in the near-infrared. 1550nm lasers are commonly used in telecom, LiDAR, and other applications requiring eye-safe design features. Manufactured from S-TiH6 or N-SF6 substrates and polished through a computer numerical controlled (CNC) process, these aspheric lenses achieve high precision performance across the NIR spectrum. Featuring a 0.4λ RMS aspheric figure error, these lenses are ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. TECHSPEC® 1550nm Precision Near-Infrared (NIR) Aspheric Lenses are available with low numerical aperture designs for applications that require beam shape to be maintained as well as high numerical aperture designs for light-gathering applications. For custom designed CNC polished aspheric lenses, please contact us.

