

150µm Aperture Diameter, Mounted, Precision Pinhole



150µm Aperture Diameter, Mounted, Precision Pinhole, #84-068

Stock **#84-068** 5 In Stock

-

1

+

£67<sup>20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £67.20 each                   |
| Qty 6-10       | £59.36 each                   |
| Qty 11+        | £54.88 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                          |                      |
|----------------------------------|----------------------|
| Mounted                          | Type:                |
| Physical & Mechanical Properties |                      |
| 25 +0.4/-0.000                   | Outer Diameter (mm): |
|                                  | Construction:        |

|                 |                               |
|-----------------|-------------------------------|
| Stainless Steel |                               |
| 150             | Fixed Aperture Diameter (µm): |
|                 |                               |
| 0.03 Nominal    | Thickness (mm):               |
|                 |                               |
| ±5              | Aperture Tolerance (µm):      |
|                 |                               |
| ±125            | Aperture Centration (µm):     |
|                 |                               |

Threading & Mounting

|                       |  |
|-----------------------|--|
| Mount Thickness (mm): |  |
| 1.25 ±0.05            |  |

Regulatory Compliance

|                             |  |
|-----------------------------|--|
| RoHS 2015:                  |  |
| <a href="#">Compliant</a>   |  |
| Certificate of Conformance: |  |
| <a href="#">View</a>        |  |
| Reach 247:                  |  |
| <a href="#">Compliant</a>   |  |

## Product Details

- Available in Aperture Mounts for a Secure Mechanical Support
- Pinhole Sized Ranging from 1 to 1,000 Microns
- [High Power Apertures](#) Available

### Unmounted Precision Pinholes

Precision Pinholes are high quality apertures centered to ±0.002" (50 microns). They are constructed of stainless steel and are 3/8" (9.5mm) in diameter. Smaller diameter pinholes will reduce energy throughput, while larger diameter pinholes will pass more spatial noise. Precision pinholes have sizes ranging from 1 to 1,000 microns. Typical applications include leak detection, aerosol studies, holography, fiber optics guides, spatial filtering, research, and more.

Use the [Precision Pinhole Mount](#) to integrate unmounted pinholes into a variety of mechanical components easily.

### Mounted Precision Pinholes

Precision Pinholes are available in aperture mounts for secure mechanical support. The mounts also fit into various optical assemblies. Each 9.5mm diameter pinhole is sealed within a 25mm diameter black-anodized aluminum mount. The mount is clearly labeled with a pinhole aperture diameter for easy identification.

**Note:** Aperture Centering to Mount ±125 microns.

Edmund Optics offers a wide selection of precision pinholes for leak detection, aerosol studies, holography, fiber optic guides, spatial filtering, research, and more. These pinholes are available in a range of diameters and are ideal for controlling light propagation. Each pinhole is manufactured using high-accuracy techniques, providing consistent circular aperture geometry and high edge quality. Available in both mounted and unmounted formats, these pinholes support a variety of optical setups, from experimental labs to industrial environments.

## Technical Information

