

TECHSPEC[®] 15mm Dia., 0.33 Numerical Aperture, Uncoated, Precision Aspheric Lens



TECHSPEC[®] Precision Aspheric Lenses

Stock **#37-422** **6 In Stock**

☐ [Other Coating Options](#)

-

1

+

£255²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£255.20 each
Qty 6-10	£229.60 each
Qty 11-25	£209.60 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Aspheric Lens	Type:
Physical & Mechanical Properties	
15.00 +0.00/-0.025	Diameter (mm):

<3	Centering (arcmin):
13.75	Clear Aperture CA (mm):
6.25	Edge Thickness ET (mm):
8.79 ±0.10	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:

Optical Properties	
22.50 @ 587.6nm	Effective Focal Length EFL (mm):
0.33	Numerical Aperture NA:
16.71	Back Focal Length BFL (mm):
N-BK7	Substrate: ☐
587.6	Aspheric Design Wavelength (nm):
0.4λ	Asphere Figure Error, RMS @ 632.8nm:
Uncoated	Coating:
40-20	Surface Quality:
1.50	f/#:
350 - 2200	Wavelength Range (nm):
Infinite	Conjugate Distance:
44.44	Power (diopters):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details

- Improved Versions of Our Aspheric Lenses
 - Precision Grade Aspheric Surfaces
 - High Numerical Apertures to Maximize Throughput
- TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

Compatible Mounts