

TECHSPEC® 15mm Dia. x 25mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-334-INK** [CONTACT US](#)

[Other Coating Options](#)

- 1 + **£95.20**

ADD TO CART

Qty 1-5
£95.20
Qty 6+
£76.08
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
15.00 ±0.025

Effective Focal Length EFL (mm):

25.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 20.98
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 14.00
Centering (arcmin): <1
Center Thickness CT (mm): 8.03 ±0.20
Center Thickness CT 1 (mm): 6.27 ±0.10
Center Thickness CT 2 (mm): 1.76 ±0.10
Radius R ₁ (mm): 17.97
Radius R ₂ (mm): -11.20
Radius R ₃ (mm): -85.31
Edge Thickness ET (mm): 6.06
Substrate:  S-BAH11 / N-SF10
Surface Quality: 40-20
f/#: 1.67
Numerical Aperture NA: 0.30
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View