

[See all 12 Products in Family](#)

TECHSPEC® 15mm Dia., VIS Coated, Linear Glass Polarizer (XP42)



Stock #19-648 **5 In Stock**

⊖ 1 ⊕ £120⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£120.00 each
Qty 10-25	£106.72 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Physical & Mechanical Properties

15.00 **Diameter (mm):**

2.00 ±0.10 **Thickness (mm):**

Dimensional Tolerance (mm):
+0.00/-0.20

Construction:
Laminated Glass Polarizing Film

Optical Properties

Coating:
VIS AR Coated

Extinction Ratio:
9000:1 @ 546nm

Substrate:
XP42 Laminated Between Glass

Transmission (%):
45 @ 546nm

Coating Specification:
R_{avg} <0.5% @ 425 - 700nm

Wavelength Range (nm):
425 - 700

Polarization Efficiency (%):
>99.98 @ 546nm

Environmental & Durability Factors

Operating Temperature (°C):
-10 to +55

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 235:
Compliant

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Uncoated and Visible AR Coated Options
- >99.98% Polarization Efficiency
- 42% Transmission for Uncoated and 45% Transmission for AR Coated Versions
- XP42 [Plastic](#) and [Film](#) Also Available

TECHSPEC® High Contrast Glass Linear Polarizers (XP42) are a high transmission, high efficiency solution that are ideal for a broad range of industrial and laboratory applications. Featuring a >99.98% polarization efficiency and an extinction ratio of 9000:1, these polarizers are constructed with an [XP42 high contrast linear polarizing film](#) laminated between two pieces of optical grade glass. TECHSPEC High Contrast Glass Linear Polarizers (XP42) are available uncoated or with a visible AR coating that provides increased transmission from 425 – 700nm. Typical single filter transmission with randomly polarized incident light is 42% for the uncoated options and 45% for the AR coated options.